
Technical sheet

BTC60BATFLEX

Swing gate suitable for Ø 60 mm barrier

This swing gate is designed to fit barriers with a diameter of 60 mm, offering a simple, robust and flexible access solution. It is designed for industrial or logistics environments requiring a pedestrian opening in an existing barrier structure. Thanks to its AISI 316 stainless steel hinges and stainless steel fasteners, it guarantees excellent corrosion resistance and long-lasting durability.











Customs code	7326909890
EAN	3321360117090

Color : Yellow

Material : Galvanized steel

Specifications :

- Swing gate with one-way opening, compatible with modular barrier.
- Tube diameter 60 mm.
- Fitted with 2 removable catches to secure the door if required.
- Compatible with the BTC60STOP stop post, which allows the door to be secured in the closed position.
- Offset fixing plate 150 x 60 mm with 4 holes Ø 14 mm.
- Fixings optional.
- Do not install in saline or hydrocarbon environments.

Length (mm)	Height (mm)	Net weight (kg)
877	405	6,80

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France

Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com