



Switches > Tactile Switches



Contact Current Rating: 50 mA

Actuator Style: Round Actuator

Operating Function: Yes

Contact Base Material: Stainless Steel

Switch Contact Plating Material: Silver

Features

Product Type Features

Leg Style	Gull Wing
Switch Connection Type	Printed Circuit Board
Illuminated	With
Actuator Style	Round Actuator

Configuration Features

Switch Feedback Type	Tactile
ESD Grounding Terminal	With
Ganged	With
Operating Function	Yes
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------

Body Features

Case Material	Thermoplastic (LCP)
Actuator Profile	Extended
Case Color	Black
Actuator Material	Thermoplastic



Cover Material	Nickel, Silver
Actuator Force	160 g[5.64 oz]
Product Orientation	Vertical
Actuator Color	Black

Contact Features

Contact Current Rating	50 mA
Contact Base Material	Stainless Steel
Switch Contact Plating Material	Silver

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	With
Process Sealed	Yes

Dimensions

Button Width	3.27 mm[.129 in]
Product Height	3.3 mm[.129 in]
Actuator Length	.9 mm[.035 in]

Usage Conditions

Operating Temperature Range	-35 – 85 °C
-----------------------------	-------------

Industry Standards

IP Rating	IP67
-----------	------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247)



Does not contain REACH SVHC


Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Reflow solder capable to 260°C
---------------------------	--------------------------------


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2-1977223-8  
FSM14JSMAS=6MM TACT SWITCH, SMT 160gf




TE Part # 2-1825910-7  
FSM14JH=6MM TACT SWITCH, HIGH TEMP




TE Part # 1977265-1  
6MM Sealed Tact switch, SMT




TE Part # 3-1437565-0  
FSM2JSMATR=ON T/R



TE Part # 4-1437565-2  
FSM4JSMATR=TACT SWITCH 6X6MIL




TE Part # 1977265-2  
6MM Sealed Tact switch, SMT on T&R




TE Part # 1825910-6  
FSM4JH=6MM TACT SWITCH, HIGH TEMP


Customers Also Bought




TE Part #1775470-5  
HPI CONN., 2.0MM, V/T, SMT, 5P, 80U"



TE Part #5-2301995-4  
RJ45 JACK INT.MAG. 1GB LED 1X1 VERT.




TE Part #2301995-4  
RJ45 JACK INT.MAG. 1GB LED 1X1 VERT.




TE Part #2434804-1  
5 position tactile, 7.5x7.5




TE Part #1734366-2  
Std USB Type A, VT, T/H, White



TE Part #2425755-1  
5 position tactile, 12x12




TE Part #1-2834016-4  
4POS 2.54MM SES CONN.



TE Part #1735042-6  
1MM FFC SMT V ASSY 6P EMBOSS



TE Part #6368150-1  
MJ,TE,8P,CAT5,SHIELDED



TE Part #281696-4  
HEADER HE13 STRAIGHT 4 P

Documents

Product Drawings

SWITCH,TACT,SMT,SEALD,GRND,T&R

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1571296-2\_G.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1571296-2\_G.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_CVM\_1571296-2\_G.2d\_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES\_CORE\_PROGRAM\_CATALOG

English

Products for Mobile Equipment

English