

SENTRON, measuring device, 7KT PAC1600, LCD, L-N: 230 V, 65 A, strd rail instr., sing.-ph., S0 + MID, apparent/active/ reactive energy, self-powered, screw terminals



Model	
Product brand name	SENTRON
Design of the product	basic
Product type designation	Measuring instrument
Type of measured value detection	complete
General technical data	
Operating mode for measured value detection	
• automatic line frequency detection	Yes
• set at 50 Hz	No
• set to 60 Hz	No
Pulse duration	
• initial value	100 ms
• Full-scale value	100 ms
Voltage curve	Sinusoidal or distorted
Measurable line frequency / initial value	45 Hz
Measurable line frequency / Full-scale value	66 Hz
Measuring procedure / for voltage measurement	TRMS
Supply voltage	

Type of voltage / of the supply voltage	self-powered
Consumed active power	
<ul style="list-style-type: none"> • without expansion module / typical 	0.45 W
Protection class	
Protection class IP	
<ul style="list-style-type: none"> • on the front 	IP40
<ul style="list-style-type: none"> • Rear side 	IP20
Electricity	
Measurable current / 2 / at AC / Rated value	65 A
Suitability	
Suitability for operation	Standard mounting rail device
Product function	
Product function	
<ul style="list-style-type: none"> • reactive power measurement 	Yes
<ul style="list-style-type: none"> • frequency measurement 	Yes
<ul style="list-style-type: none"> • voltage measurement 	Yes
<ul style="list-style-type: none"> • Current measurement 	Yes
<ul style="list-style-type: none"> • active power measurement 	Yes
Display and operation	
Design of the display	LCD
Number of keys	1
Inputs Outputs	
Number of digital outputs	1
Number of digital inputs	0
Type of switching output	solid state
Type of electrical connection	
<ul style="list-style-type: none"> • at the digital outputs 	screw-type terminals
Output current	
<ul style="list-style-type: none"> • at digital output / for signal <1> / maximum 	50 mA
<ul style="list-style-type: none"> • at the digital outputs / at DC / limited to 100 ms / maximum 	50 mA
Operating conditions for digital inputs / external voltage supply	No
Operating voltage / as output voltage / at DC / maximum permissible	30 V
Measuring inputs	
Measurable supply voltage	
<ul style="list-style-type: none"> • between (PE)N and L / at AC / minimum 	187 V
<ul style="list-style-type: none"> • between (PE)N and L / at AC / maximum 	264 V

<ul style="list-style-type: none"> • between (PE)N and L / at AC / maximum rated value 	230 V
Measuring category / for voltage measurement	CATIII
Continuous current / at AC / maximum permissible	63 A
Measuring category / for current measurement	CATIII
Relative measurable current / at AC	
<ul style="list-style-type: none"> • minimum • maximum 	0.8 % 100 %
Apparent power consumption / for current measurement	
<ul style="list-style-type: none"> • with measuring range 5 A / per phase 	6.6 V·A
Measuring procedure / for current measurement	TRMS
Measurable current / 1 / at AC / Rated value	63 A

Connections

Type of electrical connection

- | | |
|--|--|
| <ul style="list-style-type: none"> • at the measurement inputs for voltage • at the measurement inputs for current | screw-type terminals
screw-type terminals |
|--|--|

Mechanical Design

Height	90 mm
Width	35.8 mm
Depth	63 mm
Mounting position	any
Mounting type / panel mounting	No
Net weight	148 g

Environmental conditions

Degree of pollution	2
Installation altitude / at height above sea level / maximum	2 000 m
Relative humidity / at 25 °C / without condensation / during operation	
<ul style="list-style-type: none"> • maximum 	80 %
Ambient temperature	
<ul style="list-style-type: none"> • during operation / minimum • during operation / maximum • during storage / minimum • during storage / maximum 	-25 °C 55 °C -25 °C 70 °C

Certificates

Certificate of suitability	
<ul style="list-style-type: none"> • Approval Russia 	Yes



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KT1656>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7KT1656>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KT1656

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



