

Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

RS PRO Fire Sleeve White 15m

RS Stock No.: 0733696



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

General Specifications

| Part Number | Ordering Size (mm) |
|-------------|--------------------|
| 0730389 | 4 |
| 0733504 | 6 |
| 0733505 | 8 |
| 0733506 | 10 |
| 0733507 | 12 |
| 0733508 | 14 |
| 0733509 | 16 |
| 0733510 | 19 |
| 0733511 | 22 |
| 0733512 | 25 |
| 0733681 | 28 |
| 0733682 | 32 |
| 0733683 | 35 |
| 0733684 | 38 |
| 0733685 | 41 |
| 0733745 | 44 |
| 0733686 | 51 |
| 0733688 | 57 |
| 0733689 | 63 |
| 0733690 | 70 |
| 0733691 | 76 |
| 0733692 | 83 |
| 0733694 | 89 |
| 0733695 | 95 |
| 0733696 | 102 |
| 0733697 | 114 |
| 0733698 | 127 |
| 0733699 | 140 |
| 0733701 | 152 |
| 0733702 | 168 |
| 0733703 | 180 |
| 0733704 | 203 |

Approvals

| | |
|---------------|---|
| Declarations | Compiles with EN 45545-2 Tested to ISO 11925-2 |
| Standards Met | Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2 |