

## FEATURES

- **Sintered Bronze Material:** Provides durability and wear resistance, ensuring long service life.
- **Flanged Design:** Facilitates easy installation and alignment, reducing assembly time.
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for applications with varying loads, enhancing versatility.
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Capable of handling high static loads, ensuring reliability in demanding conditions.
- **ISO 9001:2008 Certified:** Guarantees quality and consistency in manufacturing processes.

## RS PRO 1.25 in Flanged Plain Bearing

RS Stock No: 518-169



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable performance under both dynamic and static loads. Made from high-quality sintered bronze, it offers excellent durability and resistance to wear, making it ideal for use in various industrial settings.

## General Specifications

Bore Size	1.25 in
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	1.62 in
Width	1 in

## Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

