

Fieldbus System Compatible with CompoNet™ Series EX120/121/122





- **CompoNet™** is an open network for sensors and actuators to transmit data and messages at high-speed with a CIP ^{Note)} control protocol.


Note) CIP: Common Industrial Protocol

- Use of the same standard protocol as DeviceNet™ and EtherNet/IP™ enables transmission of value-added information of a manufacturing site over network layers.


The CIP for CompoNet™ shares common specifications as DeviceNet™ and EtherNet/IP™, thus enabling application transplants between these CIP networks.



EX120-SCM1 + VQ1000




EX121-SCM1 + SY5000



EX122-SCM1 + SY3000

Multiple points

Compatible with 384 slaves by using a repeater




A: CompoNet™ B: DeviceNet™ C: CompoBus/S

2 types of communication cables

Can use a round (VCTF) cable (which is more available and inexpensive) or a dedicated flat ribbon cable (which is made by pressure welding and excels in workability), or both cables.




Round (VCTF) cable




Flat ribbon cable

High-speed response

Realized high-speed data transmission of approx. 1 ms with 1024 points. Networking of devices required for high-speed response has become possible, thus contributing to reduce non-productive auxiliary process time.



Use of 2 cable types depending on the application will lead to reduction of total cost.



Fieldbus System Compatible with CompoNet™ Series *EX120/121/122*

How to Order

Manifold compatible with CompoNet™				SI unit model
Series SY	SS5Y <input type="checkbox"/> - 45SZB- <input type="checkbox"/> <input type="checkbox"/> - <input type="checkbox"/> <input type="checkbox"/> - <input type="checkbox"/> <input type="checkbox"/>			EX122-SCM1
	SS5Y <input type="checkbox"/> - 45S1ZB- <input type="checkbox"/> <input type="checkbox"/>			EX121-SCM1
Series SV	SS5V <input type="checkbox"/> - 1 <input type="checkbox"/> S3ZBD- <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/> - <input type="checkbox"/> <input type="checkbox"/>			EX120-SCM1
Series VQ	VV5Q <input type="checkbox"/> 1- <input type="checkbox"/> <input type="checkbox"/> SZB- <input type="checkbox"/> <input type="checkbox"/>			EX120-SCM1
	VV5Q <input type="checkbox"/> 1- <input type="checkbox"/> <input type="checkbox"/> SZBN- <input type="checkbox"/> <input type="checkbox"/>			EX120-SCM3

• SI unit specifications

ZB	Compatible with CompoNet™	NPN (+COM.)
ZBN	Compatible with CompoNet™	PNP (-COM.)

Note) Refer to corresponding SMC catalogue for more information about manifold.

SI unit model

EX12

-SCM

Valve interface

0	Plug-in
1	Flat ribbon cable, DIN rail mounting
2	Plug-in, DIN rail mounting

Valve common polarity

1	NPN (+COM.)
3	PNP (-COM.)

Communication protocol

CM	CompoNet™
----	-----------

Accessories

Part No.	Option	Remarks
EX9-CCM1	Communication connector	For flat ribbon cable: Pressure welding connector
EX9-CCM2	Communication connector	For round cable: Terminal block type
EX9-CP2	Power supply connector	Straight type (provided with the product)

Communication Specifications

Protocol	CompoNet™
Transmission speed	93.75 kbps, 1.5 M/3 M/4 Mbps
Configuration file	EDS file (Please download it from website.)
I/O occupation area (Inputs/Outputs)	0/16
Terminator	Not provided

Note) Please confirm the details on transmission speed and settings by downloading the operation manual from website.

Unit Specifications

Model		EX120-SCM1	EX121-SCM1	EX122-SCM1	EX120-SCM3	EX121-SCM3	EX122-SCM3
Power supply voltage	For unit	14 VDC to 26.4 VDC					
	For valve	24 VDC +10%/−5%					
Internal current consumption (Unit)		100 mA or less					
Output specifications	Output type (Valve common polarity)	NPN (+COM.)			PNP (−COM.)		
	Number of outputs	16 outputs					
	Load	Solenoid valve with light/surge voltage suppressor 24 VDC, 2.1 W or less (SMC)					
	Fail safe	HOLD/CLEAR (Setting via network)					
Environmental resistance	Enclosure	IP20					
	Operating temperature range	0 to +55°C (Valve 8 points ON) 0 to +50°C (Valve 16 points ON)					
	Operating humidity range	35 to 85% RH (No dew condensation)					
	Withstand voltage	1500 VAC for 1 minute between external terminals and housing					
	Insulation resistance	500 VDC, 2 M or more between external terminals and housing					
	Vibration resistance	10 to 55 Hz with amplitude of 0.5 mm for 2 hours in each X, Y, Z direction (During de-energizing)					
	Impact resistance	98 m/s ² 3 times in each direction of X, Y, Z direction (During de-energizing)					
Standard		CE marking					
Accessory		Power supply connector (EX9-CP2), 1 pc. <small>Note)</small>					

Note) Communication connector (on the customer side) is not provided.



Applicable Solenoid Valve Series

		EX120	EX121	EX122
SV	1000	●	—	—
	2000	●	—	—
	3000	●	—	—
	4000	●	—	—
SY	3000	—	●	●
	5000	—	●	●
VQ	1000	●	—	—
	2000	●	—	—



Series EX120/121/122

SI Unit Dimensions



EX120-SCM□



EX121-SCM□




EX122-SCM□




Wiring

● Power supply connector



No.	Terminal	Function
1	24 V	Power supply for solenoid valve, 24 VDC
2	0 V	Power supply for solenoid valve, 0 V
3	FG	Ground wire

● Communication connector ^{Note)}



No.	Terminal	Function
1	BS+	Communication power supply +end
2	BDH	Communication data High end
3	BDL	Communication data Low end
4	BS-	Communication power supply -end

Note) Only inner hook-type communication connectors are compatible.
Connector on the customer side is not provided.

	Communication connectors/Part No.		
	SMC	OMRON Corp.	Honda Tsushin Kogyo
Pressure welding connector for flat ribbon cable	EX9-CCM1	DCN4-BR4	—
Terminal block type for round cable	EX9-CCM2	—	HCN-TB4LMZG+

SMC Corporation

SMC CORPORATION
Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN
Phone: 03-5207-8249 FAX: 03-5298-5362
SMC CORPORATION All Rights Reserved

European Marketing Centre (EMC)

Zuazobidea 14, 01015 Vitoria
Tel: +34 945-184 100 Fax: +34 945-184 124
URL <http://www.smc.eu>