



Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**

Contact Mating Area Plating Material: **Silver**

Wire Size: **5 – 6 mm²**

Connector System: **Wire-to-Wire**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Test Current	35 A
--------------	------

Contact Features

Contact Mating Area Plating Material	Silver
Contact Current Rating (Max)	35 A
Contact Type	Tab
Mating Tab Width	5.84 mm[.23 in]
Mating Tab Thickness	2.67 mm[.105 in]
Contact Base Material	Copper
Contact Mating Area Plating Material Thickness	2.54 μm[100 μin]
Wire Contact Termination Area Plating Thickness	2.54 μm[100 μin]
Wire Contact Termination Area Plating Material	Silver
Wire Contact Termination Area Plating Material Finish	Bright
Contact Orientation	Right Angle
Contact Underplating Material	Copper

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	5 – 6 mm²
Accepts Wire Insulation Diameter Range	4.83 – 5.59 mm[.19 – .22 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Other

Wire/Cable Type	Discrete Wire
For Use With	CPC Connectors, G Series Connectors, M Series Connectors
Comment	Hand Tool No. 69710-1 uses Die Insert No. 90145-2 for 16 AWG and Die Insert No. 90145-1 for 14-12 AWG wire., The long pin is 0.126 inches (3.2 mm) longer than the standard pin

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 206037-2 CPC PLUG ASSEMBLY SIZE 17-3	 TE Part # 7-1579008-6 UNLOCKING TOOL	 TE Part # 90384-1 HHHT TYPE XII MALE FEMALE 10 ASSY	 TE Part # 90140-1 TYPE XII MALE FEMALE 10 DIE SET
---	--	--	--

Customers Also Bought

 TE Part #81665-3 ECONOSEAL, FLANGE GASKET	 TE Part #91503-1 CCII AMPLIMITE 20 DF PIN SKT 28-20 ASSY	 TE Part #66261-1 MALE CONTACT ASSY. (L.P.)	 TE Part #66741-2 TYPE XII FEMALE CONT (L.P.)
 TE Part #66259-4 MALE CONTACT ASSY. (L.P.)	 TE Part #206137-2 23-7 FREE HANGING RECEPT	 TE Part #788153-2 SLD CPC PLUG ASSY,11-4,REV SEX	 TE Part #91515-1 CCII TYPE III+ MNL PIN SKT 30-20 ASSY



Documents

Product Drawings

MALE CONTACT ASSY. (L.P.)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_66260-4_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_66260-4_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_66260-4_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Power Contacts

English

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Products for Aerospace and Defense

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

66260-4

Power Contacts, Contact, Silver, 10 AWG Wire Size, 5 – 6 mm² Wire Size, Wire-to-Wire, Wire & Cable, Crimp, Power & Signal, Tab

