

## Product data sheet for uvex Bamboo TwinFlex® D SG



The patented Bamboo TwinFlex® technology combines the best of both worlds in one fine 18-gauge cut protection glove (Cut Level D). The bamboo viscose on the inside feels noticeably comfortable against your skin. The thin, flexible fit and high moisture absorption ensure long-lasting comfort and high wearer acceptance. Protect yourself from external hazards. High-performance fibres offer a high level of protection against abrasion and cut hazards. Thanks to the thin aqua-polymer SoftGrip coating, the Bamboo TwinFlex® D SG offers excellent grip in dry areas and outstanding dexterity.

### Features

- Ergonomic fit
- Extremely sensitive
- Extremely light
- Good grip
- Long service life
- Extremely flexible
- Very good cutting protection
- certified skin compatibility (proDerm®)
- Excellent touchscreen capability

### Suitability for industrial working environments

- Suitable for dry and slightly damp work environments

### Manufacturer address

UVEX SAFETY Gloves GmbH & Co. KG  
 Elso-Klöver-Str. 6  
 D-21337 Lüneburg  
 uvex-safety.de

<b>Material number</b>	60092
<b>Sizes</b>	5,6,7,8,9,10,11,12,13
<b>Standard</b>	EN ISO 21420:2020, EN 388:2016 + A1:2018, EN 407:2020
<b>Standard</b>	EN 388:2016 + A1:2018: 4X31D, EN 407:2020: X1XXXX
<b>Performance classes in accordance with EN 388</b>	4 X 3 1 D
<b>Performance classes in accordance with EN 407</b>	X 1 X X X X
<b>Outer material</b>	Bamboo viscose, High-performance polyethylene (HPPE), Steel, Elastane, Recycled Polyamide (PA)
<b>Coating</b>	SoftGrip-NBR
<b>Coating surface area</b>	Palm, Fingertips
<b>Type</b>	With knitted cuff
<b>Colour</b>	Green