


## FL PSE 2TX

Order No.: 2891013



Factoryline Power-over-Ethernet modules (PSE) for midspan power supply according to IEEE 802.3af, two PoE supply ports, no configuration required, function possible with 10 and 100 Mbps networks

### Commercial data

EAN	 4 046356 076043
Pack	1
Customs tariff	85176200
Gross weight in pieces	400.00 g
Country of Origin	DE
Catalog page information	Page 105 (AX-2011)

### Product notes

WEEE/RoHS-compliant since:  
06/10/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

### Product description

Power-over-Ethernet-Module (PSE) for midspan power supply according to IEEE 802.3af. The industrial Power-over-Ethernet modules enable the common transmission of power and data according to IEEE 802.3af via the Ethernet medium. Consequently, terminal equipment, such as WLAN or Bluetooth access points, IP telephones or IP cameras can be connected to the network quickly and economically. The FL PSE 2TX is a compact stand-alone solution that converts the two standard Ethernet ports to Power-over-Ethernet ports. The FL PSE 2TX is a Plug & Play device and generates the 48 V DC required for Power-over-Ethernet from the 24 V module supply according to IEEE 802.3af.

---

**Technical data****Interfaces**

Interface 1	Ethernet
No. of ports	2 (PoE ports)
Connection method	8-pos. RJ45 female connector
Transmission physics	Ethernet RJ45
Transmission speed	10/100 MBit/s
Transmission length	100 m (Between transmitter / receiver)
Signal LEDs	PoE detection

**Function**

Basic functions	PSE/midspan, complies with IEEE 802.3af
Status and diagnostic indicators	LEDs: US, PoE detection per port

**Network expansion parameters**

Maximum conductor length ((twisted pair)	100 m
--	-------

**Supply voltage**

Supply voltage	24 V DC (via COMBICON; max. conductor cross section 2.5 mm <sup>2</sup> )
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	18.5 V DC ... 30.5 V DC
Typical current consumption	typ. 100 mA (During no load; approx. 1800 mA at 24 V at the input with maximum load and 25°C ambient temperature)

**General data**

Width	45 mm
Height	99 mm
Depth	112 mm
Mounting type	DIN rail
Type AX	Stand-alone
Weight	320 g
Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	30 % ... 95 % (no condensation)
Permissible humidity (storage/transport)	30 % ... 95 % (no condensation)

Air pressure (operation)	86 kPa ... 108 kPa (2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)
Housing material	Polyamide (PA 6.6)
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005

### Conformity with EMC directives

Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion B
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A

### Certificates



Certification cULus Recognized

Certification Ex: cULus Listed

Certifications applied for:

---

**Accessories**

Item	Designation	Description
<b>Cable/conductor</b>		
2832250	FL CAT5 PATCH 0,3	Patch cable, CAT5, assembled, 0.3 m
2832263	FL CAT5 PATCH 0,5	Patch cable, CAT5, assembled, 0.5 m
2832276	FL CAT5 PATCH 1,0	Patch cable, CAT5, assembled, 1.0 m
2832221	FL CAT5 PATCH 1,5	Patch cable, CAT5, assembled, 1.5 m
2832629	FL CAT5 PATCH 10,0	Patch cable, CAT5, assembled, 10.0 m
2832289	FL CAT5 PATCH 2,0	Patch cable, CAT5, assembled, 2.0 m
2832292	FL CAT5 PATCH 3,0	Patch cable, CAT5, assembled, 3.0 m
2832580	FL CAT5 PATCH 5,0	Patch cable, CAT5, assembled, 5.0 m
2832616	FL CAT5 PATCH 7,5	Patch cable, CAT5, assembled, 7.5 m
<b>General</b>		
0800886	E/NS 35 N	End clamp, width: 9.5 mm, color: gray

---

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford / Shropshire / TF7 4PG, England  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.  
Technical modifications reserved;