

LEDVANCE® Spot 4.5W & 6.5W

Indoor luminaires | LED spotlight | Ceiling cut-out: 68mm



Areas of application

- Hotel rooms
- Bars, restaurants
- Accent lighting
- Galleries, museums
- General illumination
- Residential interiors


Product benefits

- Direct replacement for conventional 35W and 50W halogen spotlights
- Design matches the LEDVANCE DOWNLIGHT luminaire family
- Energy savings of up to 90% compared to halogen lamp spotlights
- Functional and minimalistic design
- Easy installation with fast connection
- External driver for extended flexibility (compatible with recommended DALI drivers)
- Available certificates: CE, CB, TUEV SUED

Product features

- Luminaire efficacy: 85 lm/W
- Luminous flux: up to 550lm
- Compatible with standard ceiling cut outs of 68mm
- Colour temperature: 3000K Initial color consistency: ≤ 4 SDCM
- Beam angle: 36°
- Type of protection: IP20
- White Aluminum housing, PMMA lens
- Ambient operating temperature: -20...+45 °C
- Lifetime (L70/B50): up to 30000h
- 3-years guarantee

Technical data



Product description	GTIN (EAN)	Nominal wattage [W]	Nominal voltage [V]	Power factor [λ]	Luminous flux [lm]	Luminaire efficacy [lm/W]	Colour temperature [K]	CRI index [Ra]
Spot LED adjust 4.5W/3000K 230V IP44	4058075000124	4.5W	230V	> 0.9	360	80	3000K	>80
Spot LED adjust 6.5W/3000K 230V IP44	4058075000148	6.5W	230V	> 0.9	550	85	3000K	>80

Product description	Beam angle	Rated life time L70 / B50 [h]	Type of protection IP rating	Protection class	Product size l x w or Ø [mm]	Height h [mm]	Body colour
Spot LED adjust 4.5W/3000K 230V IP44	36°	30000	20	II	Ø80	36	white
Spot LED adjust 6.5W/3000K 230V IP44	36°	30000	20	II	Ø80	36	white

Packaging information

Product description	GTIN (EAN)	Dimensions EAN10 l x w x h [mm]	Gross weight EAN 10 [g]	Volume [dm³]	Packaging unit [Pieces/unit]
Spot LED adjust 4.5W/3000K 230V IP20	4058075000124	110 x 105 x 65	273	0.99	30
Spot LED adjust 6.5W/3000K 230V IP20	4058075000148	110 x 105 x 65	273	0.99	30

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.