



Image may differ from product. See technical specification for details.

TMHS 75

Advanced hydraulic spindle, 75 kN

The TMHS series is an advanced hydraulic spindle with an integrated hydraulic pump for force generation. The spindle contains an integrated cylinder filled with hydraulic fluid. By pumping the hydraulic fluid using the spindle's handle, the piston will advance. The piston will automatically retract by releasing the pressure relief valve. They are equipped with a safety valve, which prevents overloading of the spindle and the puller it is used with.

- Nose piece with a spring-loaded centre point, allowing the puller to be easily centered on the shaft in case a centre point is available
- Quick to operate
- Comes with a range extension pieces

Overview

Dimensions

Total spindle length	520 mm
----------------------	--------

Properties

Coating	Spindle and handle bar: chrome coated Spindle body, nose and extention pieces black phosphated
Colour	Metallic and black
Content	1× Hydraulic spindle 2× Extension pieces:50 and 100 mm Nosepiece Handle Handlebar QR code card
Hydraulic spindle, piston stroke	75 mm
Material	Alloy engineering steels, hardened and tempered Rubber
Pulling force (max)	75 kN
Recommended applications	For use as force generator with desingated SKF pullers in the dismounting of bearings, gears, pulleys and other industrial ring shaped components in industrial, construction and agricultural applications with an interference fit on the shaft.
Recommended storage temperature	-5.0 – 40.0 °C
Relative humidity	< 75%
Special features	Integrated safety valve Closed hydraulic system
Spindle nose piece	yes, ø 30 mm

Logistics

Product net weight	2.79 kg
UNSPSC code	27111712
eClass code	23-05-19-01

Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.