

Product data sheet

Characteristics

LC1E300U5

Contacteur, EasyPact

TVS, 3P(3NO), AC-3, <=440V, 300A, 240V AC coil, 50Hz



Main

Range	EasyPact
Product or component type	Contacteur
Device short name	LC1E
Contacteur application	Resistive load Motor control
Utilisation category	AC-3 AC-1
Poles description	3P
[Ue] rated operational voltage	Power circuit: <= 690 V AC 50/60 Hz
[Ie] rated operational current	300 A (at <55 °C) at <= 440 V AC AC-3 for power circuit 320 A (at <40 °C) at <= 440 V AC AC-1 for power circuit
[Uc] control circuit voltage	240 V AC 50 Hz

Complementary

Motor power kW	90 kW at 220...230 V AC 50/60 Hz 160 kW at 380...400 V 160 kW at 415 V 185 kW at 440 V 200 kW at 500 V 250 kW at 660...690 V
Pole contact composition	3 NO
[Ith] conventional free air thermal current	320 A (at 40 °C)
Irms rated making capacity	3000 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated breaking capacity	2400 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	2200 A 40 °C - 10 s for power circuit
Associated fuse rating	10 A gG at <= 690 V coordination type 1 for control circuit conforming to IEC 60947-5-1 500 A gG at <= 690 V coordination type 1 for power circuit
Average impedance	0.3 mOhm - Ith 320 A 50 Hz for power circuit
Power dissipation per pole	27 W AC-3 31 W AC-1
[Ui] rated insulation voltage	690 V conforming to IEC 60947-4-1
Overvoltage category	III
Pollution degree	3
[Uimp] rated impulse withstand voltage	8 kV coil not connected to the power circuit conforming to IEC 60947
Mechanical durability	5000000 cycles
Electrical durability	400000 Cycles AC-1 500000 cycles AC-3
Control circuit type	AC at 50 Hz
Control circuit voltage limits	0.85...1.1 Uc (55 °C):operational 50 Hz 0.35...0.55 Uc (55 °C):drop-out 50 Hz
Inrush power in VA	650 VA 50 Hz cos phi 0.9 (at 20 °C) 650 VA 60 Hz cos phi 0.9 (at 20 °C)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Hold-in power consumption in VA	10 VA 50 Hz cos phi 0.9 (at 20 °C) 10 VA 60 Hz cos phi 0.9 (at 20 °C)
Heat dissipation	8 W for control circuit
Operating time	40...65 ms on closing 100...170 ms on opening
Maximum operating rate	1200 cyc/h 55 °C
Connections - terminals	Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 1...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 1...4 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 1...2.5 mm ² - cable stiffness: flexible with cable end Power circuit: cable with lug - external diameter: 240 mm Power circuit: bars 2 - busbar cross section: 5 x 30 mm
Tightening torque	Control circuit: 1.2 N.m Power circuit: 35 N.m
Minimum switching voltage	17 V for control circuit
Minimum switching current	5 mA for control circuit
Insulation resistance	> 10 MOhm for control circuit
Non-overlap time	1.5 Ms on energisation guaranteed between NC and NO contact 1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting support	Plate

Environment

Standards	IEC 60947-1 IEC 60947-4-1 IEC 60947-5-1
Product certifications	EAC CE
IP degree of protection	IP00 conforming to IEC 60529
Permissible ambient air temperature around the device	-20...70 °C at U _c -60...80 °C storage -5...55 °C operation
Operating altitude	3000 m without derating
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open (1.5 Gn, 5...300 Hz) Vibrations contactor closed (3 Gn, 5...300 Hz) Shocks contactor open (6 Gn for 11 ms) Shocks contactor closed (7 Gn for 11 ms)
Height	206 mm
Width	213 mm
Depth	219 mm
Product weight	8.5 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.0 cm
Package 1 Width	32.5 cm
Package 1 Length	25.5 cm
Package 1 Weight	9.305 kg
Unit Type of Package 2	S06
Number of Units in Package 2	10
Package 2 Height	73.5 cm
Package 2 Width	60.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	106.05 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------