



\*\*\* spare part \*\*\* SIMATIC ET 200SP, TM Posinput 1 counter and position decoder module for RS-422 incremental encoder or SSI absolute encoder, 2 DI, 2 DQ

| General information  |  |
|--|--|
| Product type designation   | TM PosInput 1  |
| Firmware version   | V1.3   |
| <ul style="list-style-type: none"> <li>FW update possible</li> </ul>                                     | Yes  |
| usable BaseUnits   | BU type A0   |
| Product function   |  |
| <ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>   | Yes; I&M0 to I&M3  |
| <ul style="list-style-type: none"> <li>Isochronous mode</li> </ul>                                       | Yes  |
| Engineering with   |  |
| <ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul> | V13 (FW V1.0), V14 (V1.2), V15 (FW V1.3) / V13 (FW V1.0), V14 SP1 (V1.2) |
| <ul style="list-style-type: none"> <li>STEP 7 configurable/integrated from version</li> </ul>            | As of V5.5 SP3, only up to FW V1.2                                       |
| <ul style="list-style-type: none"> <li>PROFIBUS from GSD version/GSD revision</li> </ul>                 | GSD Revision 5   |
| <ul style="list-style-type: none"> <li>PROFINET from GSD version/GSD revision</li> </ul>                 | GSDML V2.3   |
| Supply voltage   |  |
| Load voltage L+  |  |
| <ul style="list-style-type: none"> <li>Rated value (DC)</li> </ul>                                       | 24 V   |
| <ul style="list-style-type: none"> <li>permissible range, lower limit (DC)</li> </ul>                    | 19.2 V   |
| <ul style="list-style-type: none"> <li>permissible range, upper limit (DC)</li> </ul>                    | 28.8 V   |
| <ul style="list-style-type: none"> <li>Reverse polarity protection</li> </ul>                            | Yes  |
| Input current  |  |
| Current consumption, max.  | 75 mA; without load  |
| Encoder supply   |  |
| Number of outputs  | 1  |
| 24 V encoder supply  |  |
| <ul style="list-style-type: none"> <li>24 V</li> </ul>   | Yes; L+ (-0.8 V)   |
| <ul style="list-style-type: none"> <li>Short-circuit protection</li> </ul>                               | Yes; electronic/thermal  |
| <ul style="list-style-type: none"> <li>Output current, max.</li> </ul>                                   | 300 mA   |
| Power loss   |  |
| Power loss, typ.   | 1.9 W  |
| Address area   |  |
| Address space per module   |  |
| <ul style="list-style-type: none"> <li>Inputs</li> </ul>   | 16 byte; 4 bytes in Fast mode  |
| <ul style="list-style-type: none"> <li>Outputs</li> </ul>  | 12 byte; 4 bytes for Motion Control, 0 bytes for Fast mode               |
| Hardware configuration   |  |
| Automatic encoding   | Yes  |
| <ul style="list-style-type: none"> <li>Mechanical coding element</li> </ul>                              | Yes  |
| <ul style="list-style-type: none"> <li>Type of mechanical coding element</li> </ul>                      | type B   |
| Digital inputs   |  |
| Number of digital inputs   | 2  |
| Digital inputs, parameterizable  | Yes  |

|   |   |
|---|---|
| Input characteristic curve in accordance with IEC 61131, type 3 | Yes   |
| <b>Digital input functions, parameterizable</b>                 |   |
| • Gate start/stop   | Yes; only for pulse and incremental encoders                    |
| • Capture   | Yes   |
| • Synchronization   | Yes; only for pulse and incremental encoders                    |
| • Freely usable digital input                                   | Yes   |
| <b>Input voltage</b>  |   |
| • Rated value (DC)  | 24 V  |
| • for signal "0"  | -5 ... +5 V   |
| • for signal "1"  | +11 to +30V   |
| • permissible voltage at input, min.                            | -30 V; -5 V continuous, -30 V brief reverse polarity protection |
| • permissible voltage at input, max.                            | 30 V  |
| <b>Input current</b>  |   |
| • for signal "1", typ.  | 2.5 mA  |
| <b>Input delay (for rated value of input voltage)</b>           |   |
| for standard inputs   |   |
| — parameterizable   | Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms   |
| — at "0" to "1", min.   | 6 µs; for parameterization "none"                               |
| — at "1" to "0", min.   | 6 µs; for parameterization "none"                               |
| for technological functions                                     |   |
| — parameterizable   | Yes   |
| <b>Cable length</b>   |   |
| • shielded, max.  | 1 000 m   |
| • unshielded, max.  | 600 m   |
| <b>Digital outputs</b>  |   |
| Type of digital output  | Transistor  |
| Number of digital outputs                                       | 2   |
| Digital outputs, parameterizable                                | Yes   |
| Short-circuit protection  | Yes; electronic/thermal   |
| • Response threshold, typ.                                      | 1 A   |
| Limitation of inductive shutdown voltage to                     | L+ (-33 V)  |
| Controlling a digital input                                     | Yes   |
| <b>Digital output functions, parameterizable</b>                |   |
| • Switching tripped by comparison values                        | Yes   |
| • Freely usable digital output                                  | Yes   |
| <b>Switching capacity of the outputs</b>                        |   |
| • with resistive load, max.                                     | 0.5 A; Per digital output                                       |
| • on lamp load, max.  | 5 W   |
| <b>Load resistance range</b>                                    |   |
| • lower limit   | 48 Ω  |
| • upper limit   | 12 kΩ   |
| <b>Output voltage</b>   |   |
| • for signal "1", min.  | 23.2 V; L+ (-0.8 V)   |
| <b>Output current</b>   |   |
| • for signal "1" rated value                                    | 0.5 A; Per digital output                                       |
| • for signal "1" permissible range, max.                        | 0.6 A; Per digital output                                       |
| • for signal "1" minimum load current                           | 2 mA  |
| • for signal "0" residual current, max.                         | 0.5 mA  |
| <b>Output delay with resistive load</b>                         |   |
| • "0" to "1", max.  | 50 µs   |
| • "1" to "0", max.  | 50 µs   |
| <b>Switching frequency</b>                                      |   |
| • with resistive load, max.                                     | 10 kHz  |
| • with inductive load, max.                                     | 0.5 Hz; Acc. to IEC 60947-5-1, DC-13; observe derating curve    |
| • on lamp load, max.  | 10 Hz   |
| <b>Total current of the outputs</b>                             |   |
| • Current per module, max.                                      | 1 A   |
| <b>Cable length</b>   |   |
| • shielded, max.  | 1 000 m   |
| • unshielded, max.  | 600 m   |

| Encoder   |   |
|---|---|
| Encoder signals, incremental encoder (symmetrical)  |   |
| <ul style="list-style-type: none"> <li>• Input voltage</li> <li>• Input frequency, max.</li> <li>• Counting frequency, max.</li> <li>• Cable length, shielded, max.</li> <li>• Signal filter, parameterizable</li> <li>• Incremental encoder with A/B tracks, 90° phase offset</li> <li>• Incremental encoder with A/B tracks, 90° phase offset and zero track</li> <li>• pulse encoder</li> <li>• Pulse encoder with direction</li> <li>• pulse encoder with one impulse signal per count direction</li> </ul> | RS 422<br>1 MHz<br>4 MHz; with quadruple evaluation<br>32 m; at 1 MHz<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes  |
| Encoder signals, incremental encoder (asymmetrical)   |   |
| <ul style="list-style-type: none"> <li>• Input voltage</li> <li>• Input frequency, max.</li> <li>• Counting frequency, max.</li> <li>• Signal filter, parameterizable</li> <li>• Incremental encoder with A/B tracks, 90° phase offset</li> <li>• Incremental encoder with A/B tracks, 90° phase offset and zero track</li> <li>• pulse encoder</li> <li>• pulse encoder with direction</li> <li>• pulse encoder with one impulse signal per count direction</li> </ul>   | 5 V TTL (push-pull encoders only)<br>1 MHz<br>4 MHz; with quadruple evaluation<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes   |
| Encoder signals, absolute encoder (SSI)   |   |
| <ul style="list-style-type: none"> <li>• Input signal</li> <li>• Telegram length, parameterizable</li> <li>• Clock frequency, max.</li> <li>• Binary code</li> <li>• Gray code</li> <li>• Cable length, shielded, max.</li> <li>• Parity bit, parameterizable</li> <li>• Monoflop time</li> <li>• Multiturn</li> <li>• Singleturn</li> </ul>  | to RS-422<br>10 ... 40 bit<br>2 MHz; 125 kHz, 250 kHz, 500 kHz, 1 MHz, 1.5 MHz or 2 MHz<br>Yes<br>Yes<br>320 m; Cable length, RS-422 SSI absolute encoders, Siemens type 6FX2001-5, 24 V supply: 125 kHz, 320 meters shielded, max.; 250 kHz, 160 meters shielded, max.; 500 kHz, 60 meters shielded, max.; 1 MHz, 20 meters shielded, max. 1.5 MHz, 10 meters shielded, max.; 2 MHz, 8 meters shielded, max.<br>Yes<br>16, 32, 48, 64 µs & automatic<br>Yes<br>Yes |
| Interface types   |   |
| <ul style="list-style-type: none"> <li>• TTL 5 V</li> <li>• RS 422</li> </ul>   | Yes; push-pull encoders only<br>Yes   |
| Interrupts/diagnostics/status information   |   |
| Substitute values connectable   | Yes; Parameterizable  |
| Alarms  |   |
| <ul style="list-style-type: none"> <li>• Diagnostic alarm</li> <li>• Hardware interrupt</li> </ul>  | Yes<br>Yes  |
| Diagnoses   |   |
| <ul style="list-style-type: none"> <li>• Monitoring the supply voltage</li> <li>• Wire-break</li> <li>• Short-circuit</li> <li>• A/B transition error at incremental encoder</li> <li>• Telegram error at SSI encoder</li> <li>• Group error</li> </ul>   | Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes  |
| Diagnostics indication LED  |   |
| <ul style="list-style-type: none"> <li>• Monitoring of the supply voltage (PWR-LED)</li> <li>• Channel status display</li> <li>• for module diagnostics</li> <li>• Status indicator forward counting (green)</li> <li>• Status indicator backward counting (green)</li> </ul>   | Yes; green PWR LED<br>Yes; green LED<br>Yes; green/red DIAG LED<br>Yes<br>Yes   |
| Integrated Functions  |   |
| Counter   | Yes   |
| <ul style="list-style-type: none"> <li>• Number of counters</li> </ul>  | 1   |

|  |  |
|--|--|
| • Counting frequency, max.                             | 4 MHz; with quadruple evaluation                                 |
| Fast mode  | Yes  |
| <b>Counting functions</b>                              |  |
| • Can be used with TO High_Speed_Counter               | Yes; only for pulse and incremental encoders                     |
| • Continuous counting                                  | Yes  |
| • Counter response parameterizable                     | Yes  |
| • Hardware gate via digital input                      | Yes  |
| • Software gate  | Yes  |
| • Event-controlled stop                                | Yes  |
| • Synchronization via digital input                    | Yes  |
| • Counting range, parameterizable                      | Yes  |
| <b>Comparator</b>                                      |  |
| — Number of comparators                                | 2  |
| — Direction dependency                                 | Yes  |
| — Can be changed from user program                     | Yes  |
| <b>Position detection</b>                              |  |
| • Incremental acquisition                              | Yes  |
| • Absolute acquisition                                 | Yes  |
| • Suitable for S7-1500 Motion Control                  | Yes  |
| <b>Measuring functions</b>                             |  |
| • Measuring time, parameterizable                      | Yes  |
| • Dynamic measurement period adjustment                | Yes  |
| • Number of thresholds, parameterizable                | 2  |
| <b>Measuring range</b>                                 |  |
| — Frequency measurement, min.                          | 0.04 Hz  |
| — Frequency measurement, max.                          | 4 MHz  |
| — Cycle duration measurement, min.                     | 0.25 µs  |
| — Cycle duration measurement, max.                     | 25 s   |
| <b>Accuracy</b>  |  |
| — Frequency measurement                                | 100 ppm; depending on measuring interval and signal evaluation   |
| — Cycle duration measurement                           | 100 ppm; depending on measuring interval and signal evaluation   |
| — Velocity measurement                                 | 100 ppm; depending on measuring interval and signal evaluation   |
| <b>Potential separation</b>                            |  |
| <b>Potential separation channels</b>                   |  |
| • between the channels and backplane bus               | Yes  |
| <b>Isolation</b>                                       |  |
| Isolation tested with                                  | 707 V DC (type test)   |
| <b>Standards, approvals, certificates</b>              |  |
| Suitable for safety functions                          | No   |
| <b>Ambient conditions</b>                              |  |
| <b>Ambient temperature during operation</b>            |  |
| • horizontal installation, min.                        | -30 °C   |
| • horizontal installation, max.                        | 60 °C; Observe derating  |
| • vertical installation, min.                          | -30 °C   |
| • vertical installation, max.                          | 50 °C; Observe derating  |
| <b>Altitude during operation relating to sea level</b> |  |
| • Installation altitude above sea level, max.          | 2 000 m; On request: Installation altitudes greater than 2 000 m |
| <b>Decentralized operation</b>                         |  |
| to SIMATIC S7-300                                      | Yes  |
| to SIMATIC S7-400                                      | Yes  |
| to SIMATIC S7-1200                                     | Yes  |
| to SIMATIC S7-1500                                     | Yes  |
| to standard PROFIBUS master                            | Yes  |
| to standard PROFINET controller                        | Yes  |
| <b>Dimensions</b>                                      |  |
| Width  | 15 mm  |
| Height   | 73 mm  |
| Depth  | 58 mm  |
| <b>Weights</b>   |  |
| Weight, approx.  | 45 g   |

---

last modified:

10/12/2023 