



Connectors > Automotive Connectors > Power Distribution Boxes > Hard Wired Box Accessories



Hardware Accessory Type: **Cover**

IP Rating: **IP67**

Sealable: **No**

Operating Temperature Range: **-40 – 80 °C [-40 – 176 °F]**

Features

Product Type Features

Hardware Accessory Type	Cover
Sealable	No

Usage Conditions

Operating Temperature Range	-40 – 80 °C[-40 – 176 °F]
-----------------------------	---------------------------

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2293416-1 ISO FUSE AND RELAY, 38 POSNUNSLD BASE	 TE Part # 2304643-4 60POS,AMP MCP 2.8,REC HSG ASSY, SLD	 TE Part # 2304643-2 38POS,HYBRID,REC HSG ASSY,SLD	 TE Part # 2304643-1 49POS,HYBRID,REC HSG ASSY,SLD
 TE Part # 1443998-1 FUSE PULLER	 TE Part # 1-968857-1 AMP MCP 2.8, CONTACT SWS	 TE Part # 828905-1 SINGLE-WIRE-SEAL(5MM HOLE)	 TE Part # CAT-AM7-FRB69 Sealed Fuse and Relay Boxes
 TE Part # 2304643-3 27POS,HYBRID,REC HSG ASSY,SLD	 TE Part # 828922-1 2,5MM CAVITY PLUG FOR 5,4MM DI		

Customers Also Bought



TE Part #T4112002041-000
M12,FEMALE,RA,A CODE,4P,PG9,
GOLD

TE Part #1456968-2
CONTACT,FEMALE, 0.64, 18 AWG, AG

TE Part #2236139-1
BLIND CONNECTOR,TE,MCON 0,5

TE Part #282536-1
S.WAY SEAL F.JPT CONTACT 2.5MM

TE Part #CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB

TE Part #1241634-3
4POS MQS REC COD C

TE Part #2297813-3
BASE ASSY, 27 POSN ISO FUSE AND
RELAY

TE Part #6-1355512-7
47 WAY ABS CONNECTOR

TE Part #2079383-4
SCREW,CAP, BUTTON SOCKET HD,
METRIC,RoHS

Documents

Product Drawings
COVER, 60 POS, W/O FUSE HOLDER
English

CAD Files
3D PDF
English

Customer View Model
ENG_CVM_1443996-2_A1.2d_dxf.zip
English

Customer View Model
ENG_CVM_1443996-2_A1.3d_igs.zip
English

Customer View Model
ENG_CVM_1443996-2_A1.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



ICT Fuse and Relay Enclosures

English

Product Specifications

Product Specification

English