




MTA 156

TE Internal #: 640385-6
PCB Mount Header, Right Angle, Wire-to-Board, 6 Position, 3.96 mm [.156 in] Centerline, Unshrouded, Tin (Sn), Through Hole - Solder, Power, MTA 156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**
PCB Mount Orientation: **Right Angle**
Connector System: **Wire-to-Board**
Number of Positions: **6**
Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Unshrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Number of Columns	6
Number of Loaded Positions	6
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle
Number of Positions	6



Number of Rows	1
Number of Power Positions	6

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	1.14mm
Mating Square Post Dimension	1.14 mm[.045 in]
PCB Contact Termination Area Plating Material Thickness	2.54 µm[100 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	10.16 mm[.4 in]
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Thickness	2.54 µm[100 µin]
Contact Type	Tab
Contact Current Rating (Max)	14.24 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Termination Post & Tail Length	3.18 mm[.125 in]
Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
PCB Mount Alignment	Without
Mating Retention	Without
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without



Housing Features

Mating Entry Location	Side
Centerline (Pitch)	3.96 mm[.156 in]
Housing Material	Thermoplastic Polyester GF

Dimensions

Connector Width	6.35 mm[.25 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
Connector Length	23.77 mm[.936 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1000
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900



ppm.



Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 640551-6 06P MTA156 COVER	 TE Part # 3-640429-6 06P MTA156 CONN ASSY 24AWG WHT	 TE Part # 3-640434-6 06P MTA156 CONN ASSY 24AWG WHT	 TE Part # 3-640428-6 06P MTA156 CONN ASSY 22AWG RED
 TE Part # 3-640426-6 06P MTA156 CONN ASSY 18AWG ORA	 TE Part # 3-640430-6 06P MTA156 CONN ASSY 26AWG BLU	 TE Part # 3-640600-6 06P MTA156 CONN ASSY 20AWG LF	 TE Part # 3-643821-6 06P MTA156 CONN ASSY 26AWG LF
 TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156	 TE Part # 643071-6 06P MTA156 FD-THRU COVER	 TE Part # 640643-6 06P MTA156 COVER F/T	 TE Part # 3-644461-6 06P MTA156 CONN ASSY 18AWG LF



TE Part # 3-643817-6
06P MTA156 CONN ASSY 18AWG
ORA

TE Part # 640251-6
06P SL156 HSG W/O LCK RAMP

TE Part # 3-640602-6
06P MTA156 CONN ASSY 24AWG LF

TE Part # 3-644463-6
06P MTA156 CONN ASSY 22AWG RED

TE Part # 3-644465-6
06P MTA156 CONN ASSY 18AWG
ORA

TE Part # 3-643820-6
06P MTA156 CONN ASSY 24AWG
WHT

TE Part # 3-644466-6
06P MTA156 CONN ASSY 20AWG YEL

TE Part # 3-644566-6
06P MTA156 CONN ASSY 22AWG LF

Also in the Series | MTA 156

Connector Caps & Covers(89)

Connector Contacts(4)

Connector Hardware(2)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(677)

Power Contacts(3)

Rectangular Power Connectors(1178)

Wire-to-Board Headers & Receptacles
(677)

Customers Also Bought

TE Part #66598-2
III+ SKT,18-14,30AU/FL,STRIP

TE Part #1-87224-4
14 MODII HDR SRST UNSHRD .100

TE Part #5-534204-4
30 MODU 2-PC CE RECP ASSY, RoHS

TE Part #640383-8
08P MTA156 HDR ASSY STR SQ SN






TE Part #1-640383-2
[12P MTA156 HDR ASSY STR SQ SN](#)



TE Part #1-640385-2
[12P MTA156 HDR ASSY SQ R/A](#)




TE Part #3-640602-8
[08P MTA156 CONN ASSY 24AWG LF](#)



TE Part #4-640602-2
[12P MTA156 CONN ASSY 24AWG LF](#)



TE Part #7-1623932-5
[CFR50 5% 2M2](#)



TE Part #5747024-3
[RFI GASKET, SIZE 1, PLATED](#)

Documents

Product Drawings

[06P MTA156 HDR ASSY SQ R/A](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_640385-6_AC.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_640385-6_AC.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_640385-6_AC.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English