

B-ALTH 80K

Pressed steel fixed castor, medium duty design, with top plate fitting, heavy duty wheel, with Blickle Extrathane® polyurethane tread, with aluminium wheel centre

EAN 4047526331122

ID 331124

Customs tariff number 87169090



Bracket: B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Wheel: ALTH series

- tread: high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A, colour yellow, non-marking, non-staining
- wheel centre: die-cast aluminium, colour silver grey

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +70 °C, temporarily up to +90 °C, reduced load capacity over +40 °C



Technical data:

Wheel Ø (D)	☞ 80 mm
Wheel width	⏏ 30 mm
Load capacity at 4 km/h	⚖ 200 kg
Load capacity (static)	⚖ 500 kg
Bearing type	⦿ ball bearing
Total height (H)	⌀ 102 mm
Mounting type	top plate
Plate size	⏏ 100 x 85 mm
Bolt hole spacing	⏏ 80 x 60 mm
Bolt hole Ø	⌀ 9 mm
Temperature resistance min	-20 °C
Temperature resistance max	70 °C
Tread and tyre hardness	92 Shore A
Unit weight	⚖ 0.5 kg
Non-marking	✓
Non-staining	✓
Antistatic	ⓧ
ESD	ⓧ
Electrically conductive	ⓧ
Corrosion-resistant	ⓧ
Heat-resistant	ⓧ
Tread hydrolysis-resistant	ⓧ
Suitable for autoclaves	ⓧ
Suitable for machine washing	ⓧ

Tread and tyre hardness

■■■■■□ 92 Shore A

Rolling resistance


■■■■■□ very good

Wear resistance

■■■■■□ excellent

Operating noise / floor surface preservation

■■■■■□ good



Product references



Corresponding swivel castor L-ALTH 80K



Wheel used ALTH 80/15K