


## FEATURES

- **Nylon Material:** Offers durability and resistance to wear and tear, ensuring long-lasting performance.
- **Length of 254 mm:** Suitable for a wide range of cable bundling needs, providing flexibility in application.
- **Tensile Strength of 55 kg:** Ensures secure fastening, preventing accidental disconnection or damage.
- **Maximum Operating Temperature of 85 °C:** Suitable for use in environments with elevated temperatures, maintaining integrity under heat.
- **UL 94 V-2 Fire Behaviour:** Provides a level of flame resistance, enhancing safety in fire-prone areas.
- **Width of 17.8 mm:** Offers a broad surface area for secure and stable bundling.
- **Non-UV Resistant:** Designed for indoor use where UV exposure is minimal.

## RS PRO Heavy Duty Cable Tie, 254mm Nylon

RS Stock No: 656-104



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO Heavy Duty Cable Tie is designed for secure and reliable bundling of cables and wires. Made from durable nylon, it is ideal for industrial applications where strength and stability are crucial. With a maximum bundle diameter of 42 mm, it provides a robust solution for organising cables efficiently.

### General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	55 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

### Mechanical Specifications

Length	254 mm
Material	Nylon
Maximum Bundle Diameter	42 mm
Width	17.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---

