

Datasheet


EES50B Series

50W External Power Supply



Features:

- 50W external power supply
- Protections: Short circuit/ Overload/ Over voltage
- Input voltage range: 100 to 240VAC
- Fully enclosed plastic case
- Efficiency: Up to 80%
- Dimensions (LxWxHmm) 111x 53x 29
- 1.2m DC cable with 2.1mm connector
- 2 year warranty
- AC inlet C8 socket
- Meets CEC level IV or V
- ErP step 2 compliant
- Designed to meet TUV, CB, CCC
- CE Approved



Part Number	Voltage	Rated Current	Efficiency	Line Regulation	Load Regulation	Ripple and Noise	MTBF
	12	4.17A	85%	1%	$\pm 5\%$	2%	500khrs
	15	3.33A	85%	1%	$\pm 5\%$	2%	500khrs
	18	2.78A	85%	1%	$\pm 5\%$	2%	500khrs
	24	2.08A	85%	1%	$\pm 5\%$	2%	500khrs
	30	1.67A	85%	1%	$\pm 5\%$	2%	500khrs
	36	1.38A	85%	1%	$\pm 5\%$	2%	500khrs
	48	1.04A	85%	1%	$\pm 5\%$	2%	500khrs