



Image may differ from product. See technical specification for details.

HA 3128

Adapter sleeve with KM lock nut and MB lock washer, metric dimensions with inch bore

Adapter sleeves are the most commonly used components for locating bearings with a tapered bore onto a cylindrical seat as they can be used on plain shafts or stepped shafts. They are slit and are supplied complete with a KM lock nut and a MB lock washer.

- Easy to install
- Complete with lock nut
- Complete with locking device

Overview

Dimensions

Bore diameter	125.413 mm
Width	97 mm
Thread designation	M140x2


Properties

Taper	1:12
Holes for oil injection	Without

Logistics

Product net weight	4.06 kg
eClass code	23-11-07-05
UNSPSC code	31163218

Technical specification



Dimensions

d_1	125.413 mm	Bore diameter
d	140 mm	Outside diameter small taper
d_3	180 mm	Outside diameter lock nut
B_1	97 mm	Width
B	22 mm	Width lock nut
B_4	24 mm	Width lock nut including lock washer
G	M140x2	Thread
	1:12	External taper

Included products

Lock nut	KM 28
Locking device	MB 28

Associated products

Hydraulic nut	HMV 28E
---------------	---------

Compatible products

Component

Lock nut with metric thread, for locking by lock washer	KM 28
Lock washer for metric lock nuts	MB 28

Recommended product

Hydraulic nut for mounting or dismounting of bearings	HMF 28E
---	-------------------------

More Information

 Product details Designs and variants General product specifications Designation system	 Tools Tool and Accessory Selector for sleeves and shafts Oil Injection Method Program
--	---



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.