

D SUB MIXED FE 10A CRIMP POWER CONT S4



Part number	09 69 182 5420
Specification	D SUB MIXED FE 10A CRIMP POWER CONT S4
HARTING eCatalogue	https://b2b.harting.com/09691825420

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	D-Sub
Identification	Mixed
Type of contact	Crimp contact
Description of the contact	Straight
Features	Tool setting: 3 for AWG 16, 2 for AWG 18 and AWG 20

Version

Termination method	Crimp termination
Gender	Female
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.5 1 mm²
Conductor cross-section	AWG 20 AWG 16
Operating current	≤10 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm
Limiting temperature	-55 +155 °C
Insertion force	≤7 N
Withdrawal force	≈5 N
Performance level	NM 30 (S4) 1



Technical characteristics

Mating cycles ≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni
Layer thickness	≥0.76 µm
Layer thickness	≥30 µinch
Material (locking)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel Lead

Commercial data

Packaging size	100
Net weight	2.02 g
Country of origin	Germany
European customs tariff number	85369010
eCl@ss	27440204 Contact for industrial connectors