

Digital input module CPX-AP-L-16NDI-PI

Part number: 8176326

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Protocol	AP
Dimensions (W x L x H)	90 mm x 106 mm x 70 mm
Type of mounting	via DIN rail
Product weight	145 g
Ambient temperature	-20 °C ... 50 °C
Storage temperature	-40 °C ... 70 °C
Relative air humidity	5 - 95% Non-condensing
Degree of protection	IP20
Corrosion resistance class CRC	0 - No corrosion stress
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Pollution degree	2
Overvoltage category	II
Max. cable length	30 m inputs 50 m system communication
Note on max. cable length	Power supply according to nominal voltage
LABS (PWIS) conformity	VDMA24364 zone III
Cleanroom suitability, measured according to ISO 14644-14	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC mark	KC-EMV
Approval	RCM
Note on materials	RoHS compliant Free of halogen
Material housing	PA66 PVC
Diagnostics via LED	Diagnostics per module Status per channel
Diagnostics per internal communication	Short circuit/overload in sensor supply Electronics/sensors overvoltage Electronics/sensors undervoltage
Max. address volume, inputs	2 Byte
Communication interface, function	System communication XF10 IN / XF20 OUT
Communication interface, connection type	2x socket

Feature	Value
Communication interface, connection technology	RJ45
Communication interface, plug pattern	00995789
Communication interface, number of pins/cores	8
Communication interface, protocol	AP
Communication interface, screened	Yes
Power supply, function	Incoming electronics/sensors and load
Power supply, connection type	Socket
power supply, connection system	Push-pull according to IEC 61984
Power supply, connection pattern	00997625
Power supply, number of pins/wires	4
Power transmission, function	Outgoing electronics/sensors and load
Power transmission, connection type	Socket
Power transmission, connection technology	Push-pull according to IEC 61984
Power transmission, plug pattern	00997625
Power transmission, number of pins/wires	4
Note regarding operating voltage	SELV/PELV fixed power supplies required Note the voltage drop
Nominal operating voltage DC	24 V
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	±25%
Max. power supply	2 x 4 A (external fuse required)
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 32 mA
Power failure bridging	10 ms
Reverse polarity protection	Yes
Electrical connection input, function	Digital input
Electrical connection input, connection type	6x socket
Electrical connection input, connector system	Push-pull according to IEC 61984
Electrical connection input, connection pattern	00997626
Electrical connection input, number of connections/cores	8
Number of inputs	16
Characteristic for inputs	To IEC 61131-2, type 3
Switching level	Signal 0: (PS – 5 V) to PS Signal 1: 0 V to (PS – 11 V)
Switching logic for inputs	NPN (negative switching) 2-wire sensors to IEC 61131-2 3-wire sensors to IEC 61131-2
Input debounce time	0.1 ms 3 ms (standard) 10 ms 20 ms
Fuse protection of inputs (short circuit)	Glass cartridge fuse
Max. residual current of inputs per module	4 A
Electrical isolation of inputs between channels	No
Electrical isolation of inputs between channel – internal communication	No