


**KEMET Part Number: PEH536JAE4470M3**  
(A551BF472M035F)

PEH536, Aluminum Electrolytic, 4,700 uF, 20%, 35 VDC, -40/+105°C



### General Information

<b>Supplier:</b>	KEMET
<b>Series:</b>	PEH536
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Description:</b>	Snap-In, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	3 Pin Short
<b>AEC-Q200:</b>	No
<b>Notes:</b>	Add 0.5mm To D And 1mm To L For Sleeving
<b>Shelf Life:</b>	156 Weeks

### Dimensions

<b>D</b>	22mm +1mm
<b>L</b>	40mm +/-2mm
<b>S</b>	10mm +/-0.1mm
<b>LL</b>	4mm +/-1mm
<b>F</b>	2mm +/-0.1mm

### Packaging Specifications

<b>Weight:</b>	17 g
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	100

### Specifications

<b>Capacitance:</b>	4,700 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	35 VDC
<b>Temperature Range:</b>	-40/+105°C
<b>Rated Temperature:</b>	105°C
<b>Life:</b>	4600 Hrs (Rated Voltage And Ripple Current At 105C), 6000 Hrs (Rated Voltage At 105C)
<b>Resistance:</b>	45 mOhms (100Hz 20C), 33 mOhms (100kHz 20C)
<b>Ripple Current:</b>	2.8 Amps (100Hz 105C), 0.2 Amps (20kHz 40C)
<b>Leakage Current:</b>	494 uA (5min 20°C)