




Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Termination Method to Wire & Cable: **Crimp**
Connector System: **Cable-to-Cable, Cable-to-Panel**
Contact Retention Within Housing: **With**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Cable-to-Cable, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Signal Positions	14
Number of Power Positions	14
Number of Positions	20
Number of Rows	5

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Primary Product Color	Blue
-----------------------	------



Contact Features

Contact Type	Pin
Contact Retention Within Housing	With
Contact Current Rating (Max)	13 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Diallyl Phthalate
Centerline (Pitch)	3.81 mm[.15 in]

Dimensions

Row-to-Row Spacing	3.3 mm[.13 in]
Connector Width	11.18 mm[.44 in]
Connector Height	39.62 mm[1.56 in]
Wire Size	30 – 14 AWG
Connector Length	23.24 mm[.915 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	203
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: tris(2-methoxyethoxy)vinylsilane (.11% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | AMP M Series

Board-to-Board Jumpers & Shunts(5)


Connector Caps & Covers(14)

Connector Hardware(46)

Connector Strain Relief(13)



PCB Headers & Receptacles(9)



Rack & Panel Connectors(1)




Rectangular Power Connectors(82)




Wire-to-Board Headers & Receptacles
(1)


Customers Also Bought



TE Part #928901-3
PL 250 REC TERMINAL 17-13 AWG
TPBR LP



TE Part #163082-2
062 PIN ASS. TYP3+



TE Part #1-726388-2
187 FASTON,TAB,TPBR




TE Part #350706-1
UMNL SPLIT PIN 24-18 PTPBR L/P




TE Part #1-1393239-3
RT114024




TE Part #770985-1
MINI UMNL PIN 26-22AWG SN LP




TE Part #160773-3
PL LP RECEPTACLE 0.5-1.5 MM2 TPBR



TE Part #726386-2
250 FASTON TAB TPBR



TE Part #1-163088-0
SPEC. PLATED



TE Part #163088-1
062 SOC.ASS. TYP3+

Documents

Product Drawings
MALE BLOCK 20 PL. MIN. RECT.

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_201356-3_AF.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_201356-3_AF.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_201356-3_AF.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[6, 14, 20 AND 41 POSITION SERIES "M" CONNECTORS](#)

English

Agency Approvals

[Agency Approval Document](#)

English