



E2E-X2MC28 2M

Proximity sensor, inductive, short SUS body M8, unshielded, 2 mm, DC, 3-wire, NPN NC, 2 m cable

Specifications

Size	M8
Mounting type	Non-flush
Sensing distance	2 mm
Overall length of sensor	37.8 mm
Thread length	20 mm
Material housing	Stainless steel
Output type	NPN
Operation mode	NC
Connection method	Cable
Cable specifications	PVC (oil-resistant)
Cable length	2 m
IO-Link function	×
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP67G/IP69K

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q) - Basic Models Index list

EN PDF 7.27 MB



E2E(Q)- XB_XC basic model Instruction Sheet

EN PDF 2.28 MB



IO-Link Series Brochure

EN PDF 6.41 MB