



Connectors > Modular Jacks & Plugs > RJ45 Connectors



Modular Jack & Plug Interface Type: **RJ45**

Port Configuration: **Single Port**

Port Matrix Configuration: **1 x 1**

Modular Jacks & Plugs Products: **RJ Type Jacks & Plugs**

Connector Contact Density: **Standard**

Features

Product Type Features

Connector Product Type	Connector Kit
Modular Jack & Plug Interface Type	RJ45
Modular Jacks & Plugs Products	RJ Type Jacks & Plugs
Grounding Options	Panel Ground

Configuration Features

Port Configuration	Single Port
Port Matrix Configuration	1 x 1
Connector Contact Density	Standard
Number of Positions	8
Number of Loaded Positions	8

Body Features

Shield Plating Material	Nickel
Shield Plating Finish	Matte
Shield Material	Copper Zinc Alloy



Modular Jack Latch Orientation	Standard - Latch Down
Connector Profile	Standard

Contact Features

Contact Current Rating (Max)	.5 A
Contact Mating Area Plating Material	Gold Flash over Palladium Nickel
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material Thickness	3.27 µm[128.74 µin]

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	1.02 mm[.04 in]
Housing Color	Gray
Housing Material	Thermoplastic

Dimensions

Connector Height	28.9 mm[1.13 in]
------------------	------------------

Operation/Application

Indicator Type	No Indicator
Shielded	Yes
Circuit Application	Signal

Industry Standards

IP Rating	IP65, IP67
UL Flammability Rating	UL 94V-0
Performance Category	Cat 6A

Packaging Features

Packaging Quantity	1
Packaging Method	Blister Pack

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series

Industrial RJ45 Variant 14




Connector Hardware(1)



RJ45 Connectors(3)


Customers Also Bought



TE Part #5552726-3
ASSY,PLUG,50 POSN, RTANG, PCB



TE Part #6-2176315-3
MELF SMA_A 12K 1% 50PPM 0204 0.4 W



TE Part #5558382-1
MJ,R/A,8P,SHLD



TE Part #5-2176315-6
MELF SMA_A 3K3 1% 50PPM 0204 0.4 W






TE Part #2015698-2
RF CA,UMCC GEN2-GEN2,0.81MM
CABLE,L100MM



TE Part #6337194-1
BATTERY CONNECTOR ASSEMBLY



TE Part #53833-1
SOLIS SPR SPADE 16-14 8



TE Part #216415-4
128P.IEC-C FEM.CONN



TE Part #154979-9
10WAY POSI-MATE TAB HSG. PANEL



TE Part #8-2176315-2
MELF SMA-A 39R 1% 50PPM 0204 0.4
W

Documents

Datasheets & Catalog Pages

1-1773733-5_RJ45_VARIANT14_FLYER

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

English