


644699-2

✓ ACTIVE

MTA 156

TE Internal #: 644699-2

PCB Mount Header, Right Angle, Wire-to-Board, 7 Position, 3.96 mm [.156 in] Centerline, Partially Shrouded, Tin (Sn), Through Hole - Solder, MTA 156

[View on TE.com >](#)[Connectors > PCB Connectors > PCB Headers & Receptacles](#)PCB Connector Type: **PCB Mount Header**PCB Mount Orientation: **Right Angle**Connector System: **Wire-to-Board**Number of Positions: **7**Centerline (Pitch): **3.96 mm [.156 in]****Features****Product Type Features**

Mixed & Hybrid Header	No
Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

Connector Contact Load Condition	Selectively Loaded
Number of Columns	7
Number of Loaded Positions	6
PCB Mount Orientation	Right Angle
Number of Positions	7

Number of Rows	1
Number of Power Positions	6

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 μm [50 μin]
Contact Size	1.14mm
Mating Square Post Dimension	1.14 mm[.045 in]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material Thickness	2.54 μm [100 μin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	11.43 mm[.45 in]
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Thickness	2.54 μm [100 μin]
Contact Type	Tab
Contact Current Rating (Max)	14.24 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Post & Tail Length	3.18 mm[.125 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Friction Lock
PCB Mount Alignment	Without
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Mating Alignment

Without

Housing Features

Mating Entry Location

Side

Right Angle Bending Side

Rear

Centerline (Pitch)

3.96 mm [.156 in]

Housing Material

Thermoplastic Polyester GF

Dimensions

Connector Width

10.79 mm [.425 in]

Connector Height

7.62 mm [.3 in]

Connector Length

27.74 mm [1.092 in]

PCB Thickness (Recommended)

1.57 mm [.062 in]

Usage Conditions

Operating Temperature (Max)

105 °C [221 °F]

Operating Temperature Range

-55 – 105 °C [-67 – 221 °F]

Operation/Application

Circuit Application

Power

Industry Standards

Compatible With Agency/Standards Products

CSA, UL

UL Rating

Recognized

Compatible With Approved Standards Products

UL E28476

Glow Wire Rating

Standard Part - Not Glow Wire

UL Flammability Rating

UL 94V-0

Packaging Features

Packaging Quantity

1000

Packaging Method

Package

Other

Position Locations Omitted

4

Number of Blocked Positions

1

Product ComplianceFor compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU


Compliant


EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **MTA 156**




Connector Contacts(4)



Connector Hardware(2)




PCB Headers & Receptacles(677)




Power Contacts(3)



Rectangular Power Connectors(1178)



Standard Rectangular Connectors(667)



Wire-to-Board Connector Assemblies & Housings(594)

Customers Also Bought

TE Part #5-146274-2
02 MODII HDR SRST B/A .100CLTE Part #5-146282-1
01 MODII HDR SRST B/A .100CLTE Part #640387-3
03P MTA156 HDR ASSY SQ R/ATE Part #640445-9
09P MTA156 HDR ASSY FL/STR SNTE Part #1-640445-4
14P MTA156 HDR ASSY FL/STR SNTE Part #1-640445-8
18P MTA156 HDR ASSY FL/STR SNTE Part #2-746610-0
50 DIP PLUG, 100CL, LEAD FREE

Documents

Product Drawings

[07P MTA156 HDR ASSY R/A W/O#4](#)

English

CAD Files

[Customer View Model](#)

[ENG_CVM_CVM_644699-2_G.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model[ENG_CVM_CVM_644699-2_G.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_644699-2_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Product Specifications**[Application Specification](#)

English

Agency Approvals[Agency Approval Document](#)

English