

**Part Number :** [2016060660](#)

**Product Description :** High Current Universal Clamp Tapping Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 1 Circuit, 4 Terminations

**Series Number :** 201606

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip

**Engineering Number :** MX-KE66



---

## Documents & Resources

### Drawings

[2016060660 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant   |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Not Contained per D(2023)8585-DC<br>(23 Jan 2024)  |
| EU RoHS            | Compliant per EU 2015/863  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | Terminal Blocks and Barrier Strip   |
| Series         | 201606  |
| Description    | High Current Universal Clamp Tapping Terminal Block, 35.00mm DIN-rail Mount, 150.0A / 600V, Grey Housing and Cover, 1 Circuit, 4 Terminations |
| Application    | Wire-to-Wire  |
| Component Type | One Piece   |
| Keyword        | HCUC  |
| Product Name   | Universal Clamp   |
| Type           | High-Current Universal Clamps   |
| UPC            | 78172551135   |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 150.0A |
| Voltage - Maximum             | 600V   |

### Physical

|                   |   |
|-------------------|---|
| Circuits (Loaded) | 1 |
|-------------------|---|

|                                |   |
|--------------------------------|---|
| Circuits (maximum)             | 1   |
| Color - Resin                  | Gray  |
| Entry Angle                    | Horizontal                                  |
| Lock to Mating Part            | None  |
| Material - Metal               | Aluminum                                    |
| Material - Plating Mating      | Tin   |
| Material - Plating Termination | Tin   |
| Material - Resin               | Polyamide                                   |
| Number of Rows                 | 2   |
| Orientation                    | Vertical                                    |
| Panel Mount                    | No  |
| Pitch - Mating Interface       | N/A   |
| Polarized to Mating Part       | N/A   |
| Stackable                      | No  |
| Temperature Range - Operating  | -40° to +105°C                              |
| Termination Interface Style    | Screw                                       |
| Wire Size (AWG)                | 1/0-6, 6+6, 8+8+8                           |
| Wire Size mm <sup>2</sup>      | 13.00+13.00, 13.00-53.00,<br>8.30+8.30+8.30 |