



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 12

Teroson SI 65 RED EGFD

SDS No. : 604106
V003.1

Revision: 04.05.2022
printing date: 09.11.2023

Replaces version from: 19.04.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Teroson SI 65 RED EGFD

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

High temperature sealant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Chronic hazards to the aquatic environment

H412 Harmful to aquatic life with long lasting effects.

Category 3

2.2. Label elements

Label elements (CLP):

Hazard statement:

H412 Harmful to aquatic life with long lasting effects.

Precautionary statement: P102 Keep out of reach of children.
 P101 If medical advice is needed, have product container or label at hand.
 P273 Avoid release to the environment.
 P501 Dispose of contents/container in accordance with national regulation.

2.3. Other hazards

Evolves acetic acid during cure.

This mixture contains components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB).

Following substances are present in a concentration $\geq 0,1\%$ and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

octamethylcyclotetrasiloxane 556-67-2	PBT/vPvB
--	----------

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
octamethylcyclotetrasiloxane 556-67-2 209-136-7 01-2119529238-36	0,025- < 0,25 % (0,25 %o- < 2,5 %o)	Aquatic Chronic 1, H410 Repr. 2, H361f Flam. Liq. 3, H226	M chronic = 10	SVHC PBT/vPvB

**For full text of the H - statements and other abbreviations see section 16 "Other information".
 Substances without classification may have community workplace exposure limits available.**

SECTION 4: First aid measures

4.1. Description of first aid measures

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water, seek medical advice if necessary.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Ensure adequate ventilation.

Avoid contact with skin and eyes.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Ensure that workrooms are adequately ventilated.

Avoid skin and eye contact.

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.

Store in a cool, dry place.

Temperatures between + 5 °C and + 25 °C

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

High temperature sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Diiron trioxide 1309-37-1 [ROUGE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [ROUGE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [IRON OXIDE, FUME (AS FE)]		5	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [IRON OXIDE, FUME (AS FE)]		10	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECLTV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECLTV
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):		EH40 WEL
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Diiron trioxide 1309-37-1 [IRON OXIDE]		5	Time Weighted Average (TWA):		IR_OEL
Diiron trioxide 1309-37-1 [ROUGE RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Diiron trioxide 1309-37-1 [IRON OXIDE]		10	Short Term Exposure Limit (STEL):	15 minutes	IR_OEL
Diiron trioxide 1309-37-1 [ROUGE]		10	Time Weighted Average (TWA):		IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Acetic acid 64-19-7 [ACETIC ACID]	10	25	Time Weighted Average (TWA):	Indicative	ECLTV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	Indicative	ECLTV
Acetic acid 64-19-7 [ACETIC ACID]	20	50	Short Term Exposure Limit (STEL):	15 minutes Indicative OELV	IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Octamethylcyclotetrasiloxane 556-67-2	aqua (freshwater)		0,0015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	aqua (marine water)		0,00015 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sewage treatment plant (STP)		10 mg/l				
Octamethylcyclotetrasiloxane 556-67-2	sediment (freshwater)				3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	sediment (marine water)				0,3 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	oral				41 mg/kg		
Octamethylcyclotetrasiloxane 556-67-2	Soil				0,54 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - systemic effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	Workers	inhalation	Long term exposure - local effects		73 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - systemic effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	inhalation	Long term exposure - local effects		13 mg/m3	
Octamethylcyclotetrasiloxane 556-67-2	General population	oral	Long term exposure - systemic effects		3,7 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Combination filter: ABEKP (EN 14387)

This recommendation should be matched to local conditions.

Hand protection:

Not needed.

Eye protection:

Not needed.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state

solid

Delivery form

paste

Colour

red

Odor

specific

Flammability

The product is not flammable.

Explosive limits	Not applicable, Product is a solid.
Flash point	Not applicable
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Insoluble
Density (20 °C (68 °F))	1,25 g/cm ³ Density of pasty masses (immersion weighing method)
Relative vapour density:	Not applicable, Product is a solid.
Particle characteristics	Not applicable, mixture is a paste.

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

Evolves acetic acid during cure.

SECTION 11: Toxicological information

1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
octamethylcyclotetrasiloxane 556-67-2	LD50	> 4.800 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
octamethylcyclotetrasiloxane 556-67-2	LD50	> 2.375 mg/kg	rat	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	LC50	36 mg/l	dust/mist	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	not irritating		rabbit	equivalent or similar to OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
octamethylcyclotetrasiloxane 556-67-2	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	negative	bacterial gene mutation assay	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
octamethylcyclotetrasiloxane 556-67-2	negative	in vitro mammalian chromosome aberration test	with and without		equivalent or similar to OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
octamethylcyclotetrasiloxane 556-67-2	negative	mammalian cell gene mutation assay	with and without		equivalent or similar to OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
octamethylcyclotetrasiloxane 556-67-2	negative	inhalation		rat	equivalent or similar to OECD Guideline 475 (Mammalian Bone Marrow Chromosome Aberration Test)
octamethylcyclotetrasiloxane 556-67-2	negative	oral: gavage		rat	equivalent or similar to OECD Guideline 478 (Genetic Toxicology: Rodent Dominant Lethal Test)

Carcinogenicity

No data available.

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
octamethylcyclotetrasiloxane 556-67-2	NOAEL P 300 ppm NOAEL F1 300 ppm	two-generation study	inhalation	rat	equivalent or similar to OECD Guideline 416 (Two-Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
octamethylcyclotetrasiloxane 556-67-2	LOAEL 35 ppm	inhalation	6 h nose only inhalation 5 days/week for 13 weeks	rat	OECD Guideline 412 (Repeated Dose Inhalation Toxicity: 28/14-Day)
octamethylcyclotetrasiloxane 556-67-2	NOAEL 960 mg/kg	dermal	3 w 5 d/w	rabbit	equivalent or similar to OECD Guideline 410 (Repeated Dose Dermal Toxicity: 21/28-Day Study)

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	NOEC	0,0044 mg/l	93 d	Salmo gairdneri (new name: Oncorhynchus mykiss)	EPA OPPTS 797.1600 (Fish Early Life Stage Toxicity Test)
octamethylcyclotetrasiloxane 556-67-2	LC50	Toxicity > Water solubility	96 h	Oncorhynchus mykiss	EPA OTS 797.1400 (Fish Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	EC50	Toxicity > Water solubility	48 h	Daphnia magna	EPA OTS 797.1300 (Aquatic Invertebrate Acute Toxicity Test, Freshwater Daphnids)

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	NOEC	7.9 µg/l	21 d	Daphnia magna	EPA OTS 797.1330 (Daphnid Chronic Toxicity Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	EC50	Toxicity > Water solubility	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)
octamethylcyclotetrasiloxane 556-67-2	EC10	0,022 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	EPA OTS 797.1050 (Algal Toxicity, Tiers I and II)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
octamethylcyclotetrasiloxane 556-67-2	EC50	Toxicity > Water solubility	3 h	activated sludge	ISO 8192 (Test for Inhibition of Oxygen Consumption by Activated Sludge)

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
octamethylcyclotetrasiloxane 556-67-2	not readily biodegradable.	aerobic	3,7 %	29 d	OECD Guideline 310 (Ready BiodegradabilityCO ₂ in Sealed Vessels (Headspace Test)

12.3. Bioaccumulative potential

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
octamethylcyclotetrasiloxane 556-67-2	12.400	28 d		Pimephales promelas	EPA OTS 797.1520 (Fish Bioconcentration Test-Rainbow Trout)

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
octamethylcyclotetrasiloxane 556-67-2	6,488	25,1 °C	OECD Guideline 123 (Partition Coefficient (1-Octanol / Water), Slow-Stirring Method)

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
octamethylcyclotetrasiloxane 556-67-2	Fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080410

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Maritime transport in bulk according to IMO instruments**
not applicable

SECTION 15: Regulatory information

No information available:

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H226 Flammable liquid and vapor.

H361f Suspected of damaging fertility.

H410 Very toxic to aquatic life with long lasting effects.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.