



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin (Sn)**

Product Terminates To: **Printed Circuit Board**

Contact Current Rating (Max): **45 A**

Circuit Application: **Power**

Features

Contact Features

Contact Type	Pin
Contact Mating Area Plating Material	Tin (Sn)
Contact Current Rating (Max)	45 A

Termination Features

Rectangular Termination Post & Tail Width	1.27 mm[.05 in]
Rectangular Termination Post & Tail Thickness	.81 mm[.031 in]
Product Terminates To	Printed Circuit Board

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #1-282858-2

12P. TERMI-BLOK PCB MOUNT 90



TE Part #F37498-000

55LF0114-26-2



TE Part #5175475-5

CHAMP 050 B/B REC V W/LEG 40P



TE Part #8-2176414-1

7W STD M/OX 5% 43K



TE Part #1-1956171-7

RY531024R



TE Part #1744340-1

PCB CONTACT,CU/AG,STRAIGHT,45A



TE Part #2842122-6

6P,2MM,BRK HDR,SRRT,2,8,0.1AU,BOX



TE Part #2273101-2

M12 x 1.0 angled socket pigt shld A



TE Part #2-2176322-5

SMV 1W 10M 5%



TE Part #4-1415419-0

0419 11 1201 00

Documents

Product Drawings

PCB CONTACT,CU/AG,R/A,45A,SHOR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1744340-2_A_c-1744340-2-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1744340-2_A_c-1744340-2-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1744340-2_A_c-1744340-2-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English