

TECHNICAL DATA

Coil Type – 2.00” MEM503  
Voltage – 230v 50Hz

Coil Resistance at 21°C. –  
44.6 Ohms

Input Power at 230V 50Hz–  
40 Watts

Nominal Current at 230v 50Hz –  
0.31 Amps

Stall Current at 230v 50Hz –  
0.49 Amps

Output torque of motor – 300g/cm

Thermal Protection –  
140° Thermostat

Duty Cycle – Continuous


No Load Speed at 230v 50Hz –  
2850rpm.

Output Shaft Rotation when viewed  
from front – CCW.

Temp Heat Rise –  
21°C – 112°C / 3hrs



VIEW FROM  
FRONT



LABEL DETAILS



6.35mm Male  
Tags

Dimensions in mm

MELLOR ELECTRICS Ltd  
BLACKBURN ENGLAND

DESCRIPTION  
MEM503 230v 50Hz – 2.00”

CUSTOMER  
RS COMPONENTS

DRAWN LC 20/03/15

PART No  
AC1116