

FEATURES

- **Stainless Steel Case:** Provides excellent durability and resistance to corrosion, ensuring long-term performance.
- **Accuracy $\pm 2.5\%$:** Delivers precise pressure readings, crucial for maintaining system efficiency and safety.
- **3/8 in NPT Male & Female Connection:** Offers versatile installation options, enhancing compatibility with various systems.
- **Calibrated:** Ensures the gauge is ready for immediate use, saving time and effort in setup.
- **63 mm Dial Size:** Allows for easy reading of pressure values, improving user convenience.
- **Right Connection Location:** Facilitates straightforward integration into existing setups, reducing installation complexity.
- **Threaded Connection Type:** Ensures secure and leak-free connections, maintaining system integrity.

RS PRO 63 mm Pressure Gauge & Mounting Block

RS Stock No: 291-729



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

This RS PRO pressure gauge and mounting block is designed for precise pressure measurement in demanding industrial environments. With a robust stainless steel construction, it ensures durability and reliability. The gauge is ideal for applications requiring accurate pressure readings, offering a measurement range from 0 to 1000 bar.

General Specifications

Calibrated	Yes
Connection Location	Right
Connection Size	3/8 in
Connection Type	Threaded
Pressure Connection	3/8 in NPT Male & 3/8 in NPT Female
Product Type	Pressure Gauge & Mounting Block

Measurement Specifications

Accuracy	±2.5 %
Maximum Pressure Measurement	1000 bar
Minimum Pressure Measurement	0 bar

Mechanical Specifications

Case Material	Stainless Steel
Dial Colour	White
Dial Size	63 mm

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, CE, EN ISO 12100:2010, EN 809:1998+A1:2009, RoHS, UKCA
---------------------	--



