

Parker Product Datasheet



Parker Ball Bearing Rotary Fittings are used to connect a fixed point to a rotating, swinging or moving part via hoses. These products are used to prevent torsion and small hose radius.

PART NUMBER: DG104/12SRHDCF

SHAPE: Elbow 90°

CONNECTION 2 TYPE: Male BSPP

CONNECTION 1 TYPE: Male 24° Cone

CONNECTION 2 SIZE: G 3/8 A

CONNECTION 1 SIZE: 12 mm (O.D.)

ACCESSORIES INCLUDED: Pre-assembled with Nut and EO-PSR Cutting Ring

PRODUCT OVERVIEW

Parker ball bearing rotary fittings are used to connect a fixed point to a rotating, swinging or moving part via hoses. These products are used to prevent torsion and small hose radius.

The ball bearing rotary fittings are suitable for hydraulic oils and lubricants on mineral oil base as flow media.

The construction of this service-proved product range is characterized by a compact, maintenance-free construction. The ball bearing rotary fittings have a combined ball and plain bearing with constant lubrication, a low starting torque and wear-resistant annular piston sealings.

Markets:

- Chemical Industries
- Plant engineering
- Power stations
- Cable storage

Applications:

- Suitable for general hydraulic applications.

Features/ Benefits of the ball bearing rotary fittings:

- Parker ball bearing rotary fittings help to avoid torsion of hoses and therefore improve the life cycle of these products
- Parker ball bearing rotary fittings have a high corrosion resistant surface.
- The construction of the ball bearing fittings is maintenance-free, so that the costs for maintenance will be reduced.

Technical specifications:

Materials: Casing, body nut of steel. Annular piston sealing: POM/FKM. Eolastic sealing: NBR, also available in FKM.

Nominal temperatures: -40 °C up to +95 °C

Construction Systems:

8 different versions with one rotational axis. Multiaxial rotary couplings on request. Tube connections according to DIN 2353, series S. Maximum working pressure 350 bar (peak pressure)

Male stud sealing by Eolastic seals of NBR

Male stud with metric parallel or BSPP thread.

TECH SPECIFICATIONS

FOR FLUID TYPE	Chemicals
FOR FLUID TYPE	Hydraulic Fluids
INDUSTRY	Agriculture
INDUSTRY	Industrial Manufacturing Equipment
BRAND	Ermeto
MAXIMUM AMBIENT TEMPERATURE	572 °F
DIVISION	High Pressure Connectors Europe Division
PRODUCT STYLE	Stud Fitting
CONNECTION 2 TYPE	Male
INDUSTRY	Automotive
MINIMUM AMBIENT TEMPERATURE	-40 °C
TECHNOLOGY	Fluid & Gas Handling
MAXIMUM FLUID TEMPERATURE	572 °F
SEAL MATERIAL	NBR
CONNECTION 2 TYPE	BSPP
INDUSTRY	Marine
CONFIGURATION	Tube to Port
MAXIMUM AMBIENT TEMPERATURE	300 °C
MAXIMUM FLUID TEMPERATURE	300 °C
PRODUCT STYLE	Rotary
PRODUCT SERIES	EO Heavy
INDUSTRY	Construction
MINIMUM AMBIENT TEMPERATURE	-40 °F
PRODUCT TYPE	Hydraulic DIN Fittings

BODY MATERIAL	Steel
SPECIFICATIONS MET	ISO 1179
FOR FLUID TYPE	Steam
CONNECTION 1 TYPE	24° Cone
SHAPE	Elbow 90°
APPLICATION	Hydraulics
MINIMUM FLUID TEMPERATURE	-40 °F
ACCESSORIES INCLUDED	Pre-assembled with Nut and EO-PSR Cutting Ring
DIVISION	High Pressure Connectors Europe Division
NOMINAL INSIDE DIAMETER	DN 10
FOR FLUID TYPE	Gases
INDUSTRY	Material Handling
APPLICATION	Chemical Transfer
APPLICATION	Packaging
CONNECTION 2 SIZE	G 3/8 A inch Thread
CONNECTION 1 TYPE	Male
SEAL TYPE	ED Seal
MAXIMUM OPERATING PRESSURE	420 bar
APPLICATION	Mobile Equipment
MINIMUM FLUID TEMPERATURE	-40 °C
FOR FLUID TYPE	Fuels
INDUSTRY	Transportation
APPLICATION	Fuel Transfer
APPLICATION	Oilfield
CONNECTION 1 SIZE	12 mm Tube O.D.