

Parker Product Datasheet



The main function of Ermeto DIN banjo fittings is to connect different numbers of tubes or hoses. This broad range of DIN fittings is available in steel and in stainless steel.

PART NUMBER: WHK04LLMOMDCF
SEAL TYPE: Sealing Ring
CONNECTION 2 SIZE: M8x1.0
CONNECTION 2 TYPE: Male Metric
SHAPE: Elbow 90°
CONNECTION 1 SIZE: 4 mm (O.D.)
CONNECTION 1 TYPE: Male 24° Cone
BODY MATERIAL: Steel
PRODUCT SERIES: EO Very Light
ACCESSORIES INCLUDED: n/a

PRODUCT OVERVIEW

Banjo fittings are used in applications with limited space that involve high working pressure levels.

In the past, the Parker banjo fitting product range has included the W H (high-pressure resistant), SWVE (compact design) and DSVW (very good flow) properties series.

Now, we have combined these 3 series to create the new WHK series, uniting all of the advantages of our former banjo fitting designs.

Besides the product features also the product safety was improved. By the new design banjo bolts can not fall out during assembly thanks to the optimized design. Above that a mix-up between metric and inch dimensions is not possible anymore.

Markets:

- Automotive
- Defence
- Energy
- Environment
- Industrial
- Infrastructure
- Machine Tools
- Materials Handling
- Mobile
- Oil and Gas
- Power Generation
- Process
- Transportation
- Water

Applications:

Suitable for general hydraulic applications.

Features/ benefits:

- High-pressure resistant (up to 420 bar)
- Compact design
- Soft-sealing system with outstanding sealing properties
- Low pressure loss thanks to optimized banjo bolt design with angled drilling
- 2-in-1: Metal sealing version available - no additional metal sealing ring required
- Improved security
- Improved warehouse management

TECH SPECIFICATIONS

MINIMUM FLUID TEMPERATURE	-40 °F
MAXIMUM FLUID TEMPERATURE	248 °F
PRODUCT TYPE	Hydraulic DIN Fittings

SPECIFICATIONS MET	DIN
MINIMUM FLUID TEMPERATURE	-40 °C
SEAL MATERIAL	Metal
CONNECTION 2 SIZE	M8x1.0 mm Thread
MAXIMUM FLUID TEMPERATURE	120 °C
TECHNOLOGY	Fluid & Gas Handling
ACCESSORIES INCLUDED	n/a
DIVISION	High Pressure Connectors Europe Division
BODY MATERIAL	Steel
MAXIMUM AMBIENT TEMPERATURE	248 °F
SPECIFICATIONS MET	ISO 8434
CONNECTION 1 SIZE	4 mm Tube O.D.
PRODUCT STYLE	Banjo
MAXIMUM AMBIENT TEMPERATURE	120 °C
FOR FLUID TYPE	Steam
CONNECTION 2 TYPE	Male
CONNECTION 1 TYPE	24° Cone
PRODUCT SERIES	EO Very Light
INDUSTRY	Agriculture
INDUSTRY	Transportation
APPLICATION	Oilfield
FOR FLUID TYPE	Gases
CONNECTION 2 TYPE	Metric
BRAND	Ermeto
APPLICATION	Packaging
SEAL TYPE	Sealing Ring

INDUSTRY	Automotive
CONNECTION 1 TYPE	Male
APPLICATION	Mobile Equipment
APPLICATION	Chemical Transfer
INDUSTRY	Industrial Manufacturing Equipment
MAXIMUM OPERATING PRESSURE	100 bar
APPLICATION	Fuel Transfer
FOR FLUID TYPE	Hydraulic Fluids
INDUSTRY	Construction
MINIMUM AMBIENT TEMPERATURE	-40 °F
APPLICATION	Hydraulics
FOR FLUID TYPE	Chemicals
INDUSTRY	Material Handling
MINIMUM AMBIENT TEMPERATURE	-40 °C
SHAPE	Elbow 90°
CONFIGURATION	Tube to Port
INDUSTRY	Marine
FOR FLUID TYPE	Fuels
DIVISION	High Pressure Connectors Europe Division