

HRLSD-SPO 125K

Levelling castor, with integrated truck lock and top plate fitting, welded steel version, nylon heavy duty wheel

EAN 4047526341282

ID 912085

Customs tariff number 87169090



Bracket: HRLSD series

- solid welded steel construction, zinc-plated, yellow-passivated, Cr6-free
- axial grooved ball bearing ISO 104 and tapered roller bearing ISO 355 in the swivel head
- dust and splash-proof
- welded guide sleeve for extremely strong truck lock
- wheels and truck lock can be levelled using a wrench (SW24)
- Grease nipple

Wheel: SPO series


- high-quality nylon 6, impact resistant, hardness 70 Shore D, extremely robust heavy-duty version, colour natural white

Other features:

- high chemical resistance to many aggressive substances
- operating temperature: -20 °C to +80 °C, reduced load capacity over +35 °C
- Floor clearance with screwed in truck lock and levelling screw

Technical data:

Wheel Ø (D)	☉	125 mm
Wheel width	⊥	40 mm
Number of wheels		2
Load capacity at 4 km/h	⚖	1,300 kg
Bearing type	⊙	ball bearing
Total height (H)	⊘	170 mm
Max. total height (h)	⊘	210 mm
Max foot floor clearance (T3)		40 mm
Mounting type		top plate
Plate size	⊞	175 x 140 mm
Bolt hole spacing	⊞	140 x 105 mm
Bolt hole Ø	⌀	14 mm
Offset (F)	⊞	70 mm
Temperature resistance min		-20 °C
Temperature resistance max		80 °C
Tread and tyre hardness		70 Shore D
Unit weight	⚖	11.8 kg
Non-marking		✓
Non-staining		✓
Antistatic	⚡	✗
ESD		✗
Electrically conductive	⚡	✗
Corrosion-resistant		✗



Tread and tyre hardness

70 Shore D

Rolling resistance



excellent

Wear resistance

good

Operating noise / floor surface preservation

satisfactory



Heat-resistant	✗	✗
Suitable for autoclaves		✗
Suitable for machine washing		✗

Product references

