

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 3.2 ... 6.4 mm, lettering field size: continuous x 10 mm

Your advantages

- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ Thanks to the continuous format, a shrink sleeve marker of the appropriate length can be created flexibly for the relevant application
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- ✓ No visible difference between retrospective marking and existing markings created with a desktop roll printer
- ✓ The shrink sleeve material provides additional electrical insulation and mechanical protection for conductors
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The material is cUL certified



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 212098
GTIN	4055626212098
Weight per Piece (excluding packing)	49.600 g
Custom tariff number	96121010
Country of origin	China
Sales Key	BG221E

Technical data

Dimensions

Length (b)	1.8 m
Width (a)	10 mm
Cable diameter	3.2 mm ... 6.4 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
---------------------------------	-------------------

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929

Technical data

Ambient conditions

Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	white
Base element material	polyolefine
Type	Shrink sleeve
Components	free from silicone, halogen, and cadmium
Material	Polyolefine
Shrink rate	2:1
Marking mounting type	slide-on
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 9.0	27400401

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929

Classifications

ETIM

ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E310982
------------------	---	---	---------