

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

SECTION 1: Identification of the substance/preparation and of the company/undertaking

1.1. Product identifier

Trade name: LGWA 2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended uses: Lubricant

1.3. Details of the supplier of the safety data sheet

Supplier

Company: SKF MAINTENANCE PRODUCTS
 Address: P.O. Box 2350
 Zip code: 3430 DT
 City: Nieuwegein
 Country: NETHERLANDS
 E-mail: sebastien.david@skf.com
 Phone: +31 306307200
 Homepage: www.skf.com

1.4. Emergency Telephone Number

Members of the public: 111 (NHS 111 (Scotland: NHS 24))

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

CLP-classification: Skin Sens. 1;H317

Most serious harmful effects: May cause an allergic skin reaction.

2.2. Label elements

Pictograms



Signal word: Warning

Contains

Substance: Naphthenic acids, zinc salts, basic

H-phrases

H317 May cause an allergic skin reaction.

P-phrases

P261 Avoid breathing dust/fume/gas/mist/vapours/spray.

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

| | |
|--|--|
| P280 P302+352 P333+313 P362+364 P501 | Wear protective gloves. IF ON SKIN: Wash with plenty of soap and water. If skin irritation or rash occurs: Get medical advice/attention. Take off contaminated clothing and wash it before reuse. Dispose of contents/container in accordance with local regulation. |
|--|--|

2.3. Other hazards

The product does not contain any PBT or vPvB substances.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

| Substance | CAS No | EC No | REACH Reg. No. | Concentration | Notes | CLP-classification |
|--|------------|-----------|------------------|---------------|-------|--|
| Dilithium azelate | 38900-29-7 | 254-184-4 | 01-2120119814-57 | 2.5 - 5% | | Acute Tox. 4;H302 |
| Naphthenic acids, zinc salts, basic | 84418-50-8 | 282-762-6 | 01-2119988500-34 | < 2.5% | | Skin Sens. 1;H317 Eye Irrit. 2;H319 Aquatic Chronic 3;H412 |
| reaction products of bis(4-methylpentan-2-yl) dithiophosphoric acid with phosphorus oxide, propylene oxide and amines, C12-14-alkyl (branched) | - | 931-384-6 | 01-2119493620-38 | < 0.25% | | Acute Tox. 4;H302 Skin Sens. 1B;H317 Eye Dam. 1;H318 Aquatic Chronic 2;H411 |

Please see section 16 for the full text of H-phrases.

Ingredient comments: The mineral oils in the product contain <3% DMSO extract(IP 346).

SECTION 4: First aid measures

4.1. Description of first aid measures

| | |
|----------------------|--|
| Inhalation: | Seek fresh air. |
| Ingestion: | Wash out mouth thoroughly and drink 1-2 glasses of water in small sips. Seek medical advice in case of discomfort. |
| Skin contact: | Remove contaminated clothing. Wash skin with soap and water. Seek medical advice in case of persistent discomfort. |
| Eye contact: | Flush with water (preferably using eye wash equipment) until irritation subsides. Seek medical advice if symptoms persist. |
| General: | When obtaining medical advice, show the safety data sheet or label. |

4.2. Most important symptoms and effects, both acute and delayed

May cause sensitization by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing.

4.3. Indication of any immediate medical attention and special treatment needed

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

No special immediate treatment required. Treat symptoms.

SECTION 5: Fire-fighting measures

5.1. Extinguishing media

Suitable extinguishing media: Extinguish with powder, foam, carbon dioxide or water mist. Use water or water mist to cool non-ignited stock.

Unsuitable extinguishing media: Do not use water stream, as it may spread the fire.

5.2. Special hazards arising from the substance or mixture

Not flammable, but combustible. Can generate harmful flue gases containing carbon monoxide in the event of fire.

5.3. Advice for fire-fighters

Move containers from danger area if it can be done without risk. Avoid inhalation of vapour and flue gases - seek fresh air. Wear Self-Contained Breathing Apparatus (SCBA) with a chemical protection suit only where personal (close) contact is likely.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel: Wear gloves. Wear safety goggles if there is a risk of eye splash. Stay upwind/keep distance from source. In case of insufficient ventilation, wear respiratory protective equipment.

For emergency responders: In addition to the above: Protective suit equivalent to EN 368, type 3, is recommended.

6.2. Environmental precautions

Prevent spillage from entering drains and/or surface water.

6.3. Methods and material for containment and cleaning up

Contain and absorb spill with sand or other absorbent material and transfer to suitable waste containers. Wipe up minor spills with a cloth.

6.4. Reference to other sections

See section 8 for type of protective equipment. See section 13 for instructions on disposal.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use the product under well-ventilated conditions. Running water and eye wash equipment should be available. Wash hands before breaks, before using restroom facilities, and at the end of work.

7.2. Conditions for safe storage, including any incompatibilities

Store safely, out of reach of children and away from food, animal feeding stuffs, medicines, etc. Keep in tightly closed original packaging. Do not expose to heat (e.g. sunlight). Store at temperatures below 45°C. Do not store with the following: Strong oxidisers.

7.3. Specific end use(s)

None.

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

- Occupational exposure limit:** Contains no substances subject to reporting requirements
- Measuring methods:** Compliance with occupational exposure limits may be checked by occupational hygiene measurements.
- Legal basis:** EH40/2005 Workplace exposure limits. Last amended January 2020.

8.2. Exposure controls

- Appropriate engineering controls:** Wear the personal protective equipment specified below.
- Personal protective equipment, eye/face protection:** Wear safety goggles if there is a risk of eye splash. Eye protection must conform to EN 166.
- Personal protective equipment, hand protection:** Wear gloves. Type of material and thickness: Nitrile rubber/ 0,38 mm. Penetration time: >8 hours. The suitability and durability of a glove is dependant on usage, e.g. frequency and duration of contact, glove material thickness, functionality and chemical resistance. Always seek advice from the glove supplier. Gloves must conform to EN 374.
- Personal protective equipment, respiratory protection:** Not required.
In case of risk of formation of spray mist, wear respiratory protective equipment with P2 filter. Respiratory protection must conform to one of the following standards: EN 136/140/145.
- Environmental exposure controls:** Ensure compliance with local regulations for emissions.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| Parameter | Value/unit |
|----------------------|------------------------------------|
| State | Fat. |
| Colour | Yellow / Brown |
| Odour | Solvent |
| Solubility | Insoluble in the following: Water. |
| Explosive properties | No data |
| Oxidising properties | No data |

| Parameter | Value/unit | Remarks |
|---|------------|---------|
| pH (solution for use) | No data | |
| pH (concentrate) | No data | |
| Melting point | No data | |
| Freezing point | No data | |
| Initial boiling point and boiling range | No data | |
| Flash Point | > 150 °C | |
| Evaporation rate | No data | |
| Flammability (solid, gas) | No data | |
| Flammability limits | No data | |
| Explosion limits | No data | |

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

| | | |
|---------------------------------------|---------|--|
| Vapour pressure | No data | |
| Vapour density | No data | |
| Relative density | No data | |
| Partition coefficient n-octanol/water | No data | |
| Auto-ignition temperature | No data | |
| Decomposition temperature | No data | |
| Viscosity | No data | |
| Odour threshold | No data | |

9.2 Other information

| Parameter | Value/unit | Remarks |
|-----------|--------------------------|---------|
| Density | < 1000 kg/m ³ | (25 °C) |

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with the following: Strong oxidisers.

10.2. Chemical stability

The product is stable when used in accordance with the supplier's directions.

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

Do not expose to heat (e.g. sunlight).

10.5. Incompatible materials

Strong oxidisers.

10.6. Hazardous decomposition products

Can generate harmful flue gases containing carbon monoxide in the event of fire.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

LGWA 2

| Organism | Test Type | Exposure time | Value | Conclusion | Test method | Source |
|----------|-----------|---------------|------------|------------|-------------|--------|
| | ATE | | 3630 mg/kg | | Calculated | |

Dilithium azelate, cas-no 38900-29-7

| Organism | Test Type | Exposure time | Value | Conclusion | Test method | Source |
|----------|-----------|---------------|------------|------------|-------------|--------|
| | LD50 | | > 300mg/kg | | | |

Naphthenic acids, zinc salts, basic, cas-no 84418-50-8

| Organism | Test Type | Exposure time | Value | Conclusion | Test method | Source |
|----------|-----------|---------------|-------------|------------|-------------|--------|
| | LD50 | | > 2000mg/kg | | | |

Ingestion may cause discomfort. The product does not have to be classified. Based on existing data, the classification criteria

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

are deemed not to have been met.

Acute toxicity - dermal

LGWA 2

| Organism | Test Type | Exposure time | Value | Conclusion | Test method | Source |
|----------|-----------|---------------|------------|------------|-------------|--------|
| | ATE | | 3625 mg/kg | | Calculated | |

Dilithium azelate, cas-no 38900-29-7

| Organism | Test Type | Exposure time | Value | Conclusion | Test method | Source |
|----------|-----------|---------------|-------------|------------|-------------|--------|
| Rat | LC50 | | > 2000mg/kg | | | |

The product does not have to be classified. Based on existing data, the classification criteria are deemed not to have been met.

- Acute toxicity - inhalation:** The product does not have to be classified. Test data are not available.
- Skin corrosion/irritation:** May cause slight irritation. The product does not have to be classified. Test data are not available.
- Serious eye damage/eye irritation:** Temporary irritation. The product does not have to be classified. Test data are not available.
- Respiratory sensitisation or skin sensitisation:** May cause sensitization by skin contact. Symptoms include reddening, swelling, blistering and ulceration - often slowly developing.
- Germ cell mutagenicity:** The product does not have to be classified. Test data are not available.
- Carcinogenic properties:** The product does not have to be classified. Test data are not available.
- Reproductive toxicity:** The product does not have to be classified. Test data are not available.
- Single STOT exposure:** The product does not have to be classified. Test data are not available.
- Repeated STOT exposure:** The product does not have to be classified. Test data are not available.
- Aspiration hazard:** The product does not have to be classified. Test data are not available.
- Other toxicological effects:** On warming/heating, the vapours emitted may cause irritation to the respiratory organs. May cause coughing and breathing difficulties.

SECTION 12: Ecological information

12.1. Toxicity

The product contains small quantities of environmentally hazardous substances. The product does not have to be classified. Test data are not available.

12.2. Persistence and degradability

Not expected to be biodegradable. Test data are not available.

12.3. Bioaccumulative potential

No bioaccumulation expected. Test data are not available.

12.4. Mobility in soil

Not expected to be mobile in soil. Test data are not available.

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

12.5. Results of PBT and vPvB assessment

The product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Oil products may cause soil and water pollution.

German water pollution classification (WGK): 1

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Avoid discharge to drain or surface water. If this product as supplied becomes a waste, it does not meet the criteria of a hazardous waste (Dir. 2008/98/EU). Disposal should be in accordance with applicable regional, national and local laws and regulations. Local regulations may be more stringent than regional or national requirements. Uncleansed packaging is to be disposed of via the local waste-removal scheme. Empty, cleansed packaging should be disposed of for recycling.

Category of waste: EWC code: Depends on line of business and use, for instance 13 08 99* wastes not otherwise specified

Absorbent/cloth contaminated with the product: EWC code: 15 02 03 Absorbents, filter materials, wiping cloths and protective clothing other than those mentioned in 15 02 02.

SECTION 14: Transport information

14.1. UN-No.: Not applicable.

14.4. Packing group: Not applicable.

14.2. UN proper shipping name: Not applicable.

14.5. Environmental hazards: Not applicable.

14.3. Transport hazard class(es): Not applicable.

14.6. Special precautions for user

None.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Special Provisions: Special care should be applied for employees under the age of 18. Young people under the age of 18 may not carry out any work causing harmful exposure to this product.

Covered by:
Council Directive (EC) on the protection of young people at work.

15.2. Chemical Safety Assessment

Other Information: Chemical safety assessment has not been performed.

SECTION 16: Other information

Safety Data Sheet

LGWA 2

Replaces date: 10/09/2019

Revision date: 19/03/2020

Version: 6.1.0

Version history and indication of changes

| Version | Revision date | Responsible | Changes |
|---------|---------------|-------------------------|---------|
| 6.1.0 | 19/03/2020 | Bureau Veritas HSE/ SRU | 8, 16 |

Abbreviations:

PBT: Persistent, Bioaccumulative and Toxic
 vPvB: Very Persistent and Very Bioaccumulative
 STOT: Specific Target Organ Toxicity

Other Information:

This safety data sheet has been prepared for and applies to this product only. It is based on our current knowledge and the information that the supplier was able to provide about the product at the time of preparation. The safety data sheet complies with applicable law on preparation of safety data sheets in accordance with 1907/2006/EC (REACH) as subsequently changed.

Training advice:

A thorough knowledge of this safety data sheet should be a prerequisite condition.

Classification method:

Calculation based on the hazards of the known components.

List of relevant H-statements

- H302 Harmful if swallowed.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H319 Causes serious eye irritation.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.

Document language:

GB