


## FEATURES

- **High hardness (Shore A 90 to 95):** Provides excellent resistance to deformation and wear
- **Wide temperature range (-20 °C to 140 °C):** Suitable for diverse thermal environments
- **Material composition (Fluorinated Ethylene Propylene, Viton):** Ensures superior chemical resistance and longevity
- **Large inside diameter (633.5 mm):** Fits a variety of industrial equipment
- **Compliance with multiple standards:** Meets BS ISO 3601-1, AS 568, FDA, and more for assured quality

## RS PRO 633.5 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-621



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in a variety of industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene and Viton, it offers excellent chemical resistance and durability. Ideal for environments with temperatures ranging from -20 °C to 140 °C, this O-Ring ensures optimal performance in demanding conditions.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	633.5 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	644.16 mm
Thickness	5.33 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	-------------------------------------------------------------------------------------------------------------------------

