


## Flex-B

### Stainless Steel Bellows Couplings, 3 Convolution with Clamp Style Fixing



#### Dimensions and Order Codes

	Coupling Size	Coupling Ref	ØD	L ±1.0	L1 (1)	ØB1, ØB2 max	Fasteners			Moment of inertia (3)	Mass (3)
			mm	mm	mm	mm	Screw	Torque (2) Nm	Wrench mm	kgm <sup>2</sup> × 10 <sup>-8</sup>	kg × 10 <sup>-3</sup>
more	20	536.20	20	31	11	8	M2.5	1.32	2	90	16
more	26	536.26	26	37.5	14	12	M3	2.43	2.5	330	34
more	34	536.34	34	40	14	16	M3	2.43	2.5	925	56
more	41	536.41	41	49.7	18	20	M4	5.66	3	2390	99

#### Table Notes:

Length of supported through bore. Shafts can near butt.  
Maximum recommended tightening torque.  
Values apply with max bores.

#### Materials & Finishes

##### Hubs:

Al. Alloy 2014 T6, Clear anodised finish.

##### Bellows:

Spring quality stainless steel.

##### Joint assembly:

Copper C106, heat treated Zinc plate, black chromate.

##### Fasteners:

Alloy Steel, black oiled

#### Temperature Range

-40°C to +120°C

#### Performance

	Coupling Size	Ref.	Peak torque (4)	Max compensation			Flexural stiffness			
				Angular (5) deg	Radial (5) mm	Axial (5) mm	Torsional (6) Nm/rad	Angular N/deg	Radial N/mm	Axial N/mm
more	20	536.20	2	2	0.06	0.35	315	1.03	115	17.7
more	26	536.26	3.2	2	0.06	0.36	755	1.27	238	5.7
more	34	536.34	7.5	2.5	0.1	0.6	1740	1.34	227	6.6
more	41	536.41	10	2.5	0.15	0.8	2880	1.58	144	13.1

#### Table Notes:

Peak torque. Select a size where Peak Torque exceeds the application torque x service factor.  
Max. compensation values are mutually exclusive.  
Torsional stiffness values apply at 50% peak torque with no misalignment, measured shaft-to-shaft with largest standard bores. Note that in some vendors' catalogues the given torsional stiffness applies to the un-mounted bellows element only, an unrepresentative calculated value.