




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Red
-----------------------	-----

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6.65 mm[.261 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 170326-1 187 PL MKII REC. 18-14AWG PTBR	 TE Part # 170324-2 PL 187 RECEPTACLE 24-20 AWG 0.3 NPCU	 TE Part # 170324-1 187 PL MKII REC. 24-20AWG PTBR	 TE Part # 170332-1 PL 187 RECEPTACLE 18-14 AWG PTPBR
 TE Part # 2-174712-1 PL MK2 2P 187 HOUSING REC NATURAL	 TE Part # 170326-5 187 PL MKII REC. 18-14AWG PTPB	 TE Part # 170330-2 PL 187 RECEPTACLE 24-20 AWG NPPHBZ	 TE Part # 170325-1 187 PL MKII REC. 20-16AWG PTBR
 TE Part # 170325-5 187 PL MKII REC. 20-16AWG PTBR	 TE Part # 170331-1 PL MKII 187 REC 20-16AWG PTBR LP	 TE Part # 170330-1 PL MKII 187 REC 24-20AWG PTBR LP	

Also in the Series | Positive Lock 187

 Crimp Terminal Housings(76)	 Insertion & Extraction Tools(2)	 Insulation Boots & Sleeves(7)	 Quick Disconnects(57)
---------------------------------	-------------------------------------	-----------------------------------	---------------------------

Also in the Series | Mark II




Automotive Connector Locks & Position Assurance(1)




Automotive Housings(6)



Automotive Terminals(3)



Connector Seals & Cavity Plugs(1)



Crimp Terminal Housings(76)



Insertion & Extraction Tools(2)



Quick Disconnects(57)

Customers Also Bought



TE Part #6-1393302-3
V23134A1053C643-EV-CBOX



TE Part #CAT-J41-DDPC
DEUTSCH DT Plug Connectors



TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #880810-1
COVER CAP , 2 WAY



TE Part #964285-2
JPT A REC 2.8 Contact SRC Sn (LP)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-174712-7_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-174712-7_M.3d_igs.zip



English

Customer View Model

ENG_CVM_CVM_1-174712-7_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Positive Lock Receptacles

English

Agency Approvals

UL Report

English