

Datasheet

Endoscope

Model: VCAMLCDCOL 9-17



TECHNICAL SPECIFICATIONS

CAMERA

- Image sensor: 1/4 "CMOS
- Viewing angle: 30/45 °
- Lighting : 4 white LEDs
- 1 Mt of length - 9mm and 17mm of diameter probes
- Degree of protection IP67
- Power supply: 4 AA batteries (not included)

MONITOR

- Display: 3.5 "color TFT-LCD Wireless
- Resolution: 640 * 480 pixels
- Wireless connection
- Recording of movies and photos on mini SD card
- USB port and cable upload/download of photos and movies
- Video output A / V
- Power supply: Rechargeable Lithium

AREAS OF USE

- Internal Cracks / Reading of serial number within equipment / Recovery of lost items / Internal inspection of pipes and wall cavity / Internal inspection of equipment / Location of cables and pipes / Control and polls of connectors and sockets electrical / Inspection and quality check / inspection of insulation / Engine internal inspection

INCLUDED IN THE PACKAGE

Plastic case

