



Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D09...D38 4P LC1DT20...DT40 4P LC1D098...D258 CAD32, CAD50

Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	Bidirectional peak limiting diode
[Uc] control circuit voltage	72 V DC
Maximum peak voltage	2 Uc
Net weight	0.012 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.