

## 832 - Die stocks



IMAGE UNAVAILABLE

### Description:

- Pressure-cast Zamak body for accurate centring of the die.
- Finish: grey hammered finish.

	Diameter [mm]	Length L [mm]	Weight [g]
832.1P	25.4	220.0	115.0
832.1P1/2	38.1	325.0	410.0