



Switches > Toggle Switches



Contact Current Rating: **20 A**
Configuration (Pole-Throw): **Double Pole - Double Throw**
Operating Function: **On Off (On)**
Number of Positions: **3**
Operating Voltage: **30 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Quick Connect Terminal
Toggle Style	Baton
Switch Type	Power Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On Off (On)
Number of Positions	3

Electrical Characteristics

Contact Resistance	10 mΩ
Insulation Resistance	1000 MΩ
Dielectric Withstanding Voltage (Max)	1500 VAC
Contact Current Rating	20 A
Operating Voltage	125 VAC, 250 VAC



Body Features

Sealing Method	Rubber O-Ring
Product Orientation	Vertical
Bushing Style	Unthreaded

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Silver Alloy

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Dimensions

Toggle Length	17.48 mm[.688 in]
---------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on




requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1-6437630-1
AWTS1504




TE Part # 2-6437630-0
FTD0904=MINIATURE TOGGLE



TE Part # 8-6437630-0
A4TK15W04




TE Part # 7-6437630-2
AWTN1504 = POWER TOGGLE




TE Part # 5-6437630-0
AWTR1504 = POWER TOGGLE


Customers Also Bought




TE Part #1624323-5
UPW50 0.1% 5PPM 120R



TE Part #1-1462039-8
IM06DGR=IM RELAY 140mW 12V



TE Part #4-1622796-6
YR1 0.1% 82K5



TE Part #7-6437630-2
AWTN1504 = POWER TOGGLE




TE Part #7-6437630-0
AWTD1504 = POWER TOGGLE



TE Part #1623569-1
CRG1206 1% 82K



TE Part #6-1419102-3
T9AP1D52-24



TE Part #1-1624323-0
UPW50 0.1% 5PPM 250R



Documents

Product Drawings

AWTT1504

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-6437630-0_B_c-1-6437630-0-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-6437630-0_B_c-1-6437630-0-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-6437630-0_B_c-1-6437630-0-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English

AW_SERIES_SWITCHES_QUICK_REF_GUIDE_1-1773458-8

English