



TE Internal #: 1-5331677-3
3.51 mm [.138 in] Socket Length, 1.57 mm [.062 in] PCB Hole,
Closed Bottom, .41 – .518 mm² Wire, 20 – 21 AWG, Cable-to-
Board, Pin Sockets
[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 5A



Socket Length: 3.51 mm [.138 in]
PCB Hole Diameter: 1.57 mm [.062 in]
Socket Sleeve Style: Closed Bottom
Wire Size: 20 – 21 AWG
[All Miniature Spring Sockets: Closed Bottom, Beryllium Copper, 5A \(11\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Closed Bottom
Connector System	Cable-to-Board
Sealable	No

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Contact Features

Contact Spring Plating Material	Tin
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	2.54 µm
Contact Spring Plating Thickness	2.54 µm[30 µin]
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder



Insertion Method	Hand/Semi-Automatic/Automatic
------------------	-------------------------------

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm[.031 – .125 in]
Socket Length	3.51 mm[.138 in]
PCB Hole Diameter	1.57 mm[.062 in]
Wire Size	20 – 21 AWG
Mating Pin Diameter Range	.76 – .84 mm[.03 – .033 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Packaging Features

Packaging Method	Bag, Loose Piece
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
-----------------	------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # 1-332070-1 SOCKET,MIN-SPR AU SER-4	TE Part # 1-332070-7 SOCKET,MIN-SPR W/KO AU SER-4	TE Part # 1-5331677-6 SOCKET,MIN-SPR SN SER-3	TE Part # 1-332070-4 SOCKET,MIN-SPR W/H AU SER-4

Customers Also Bought

			
TE Part #YDTS20W25-19SCV001 RECP ASSY	TE Part #6-1437661-0 TC8-08-PFH=COVER w/HOLES	TE Part #477643-000 DK-621-0048-2P	TE Part #453925-7 CRIMPER, WIRE-.180 WIDE F
			
TE Part #111614-4 020 STRAIN RELIEF 2MM	TE Part #41996 SPLICE 7400-10000 CMA TPBR	TE Part #86492-4 MOD IV RECP PLTD 30 SEL	TE Part #CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS



Documents

Product Drawings

[SOCKET,MIN-SPR SN SER-3U SER-3](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-5331677-3_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5331677-3_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-5331677-3_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English