

Product data sheet

Power connectors




Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06


Illustration



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	99 6156 000 06
Connector design	Female cable connector
Type standard	DIN EN IEC 61076-2-116
Version	Field-wireables
Connector locking system	Bayonet
Termination	screw clamp
Degree of protection	IP67 plugged and locked
Connection cross-section	max. 2.50 mm ² / max. AWG 14
Cable outlet	7,0-14,0 mm
Temperature range from/to	-40 °C / 85 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	138.71
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	Power: 630 V, Signal: 63 V
Rated impulse voltage	Power: 6000 V, Signal: 1500 V
Rated current	Power: 16 A, Signal: 10A
Insulation resistance	> 10 ⁸ Ω
Pollution degree	3
Overvoltage category	III
Insulating material group	II
EMC compliance	shieldable

Product data sheet

Power connectors



Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06

Material

Housing material	Zinc die-cast nickel-plated
Contact body material	PA
Contact material	CuZn (brass lead-free)
Contact plating	Ag (silver)
Locking material	Zinc die-cast nickel-plated
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	35fcb9a1-6c00-47d7-9a07-4aba6661a555

Authorization/approvals


Approvals	UL 2237
-----------	---------

Declarations of conformity

Low Voltage Directive	2014/35/EU (EN 60529:1991 2014/35/EU;EN 60204-1:2018)
-----------------------	---


Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06

Assembly instructions




1. Unscrew the clamping screws until the holes for the single wires are completely free.
2. Turn the shielding sheets of the pressing piece outwards.
3. Bead the pressing screw, matching seal and pressing piece onto the cable individually.
4. Strip the cable by about 40 mm. If connecting crosswise, strip 45 mm.
5. Shorten shield and filler by 30 mm or 35 mm when connecting crosswise, so that the single wires are exposed by 30 mm or 35 mm. If necessary, wrap shielding braid with copper tape.
6. Shorten the PE wire to 17 to 20 mm. In case of cross-over assembly, shorten wire 2 to approx. 31 mm.
7. Strip all single wires 7 to 8 mm and twist them. If necessary, crimp on ferrules. Please observe the instructions for connecting single wires with ferrules.*
8. Insert the strands into the holes until the insulation rests on the contact and tighten the clamping screws (0,5 Nm). Recommended order: contact 2, PE contact, contact 1+3, signal contacts.
9. Bring the pressing piece and male/female insert together until the pressing piece rests on the contact carrier. The shielding sheets should now be able to touch the shield. The individual wires must not protrude into the sealing area.
10. Insert the pressing piece including the male/female insert into the sleeve as far as it will go.
11. Push the seal into the pressing piece as far as it will go.
12. Screw on the pressing screw and tighten with approx. 6 Nm.

* Ferrules with insulation



Ferrules without insulation




Notes:

The ferrules must not exceed a length of 8 mm.
The single wires with ferrule should, if possible, rest on the contact.
The insulation of the ferrules with insulation may protrude a maximum of 0.8 mm over the contact.


Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06

Derating curve



Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06

Derating curve



Product description	Bayonet Female cable connector, Contacts: 6 (3+PE+2), 7,0-14,0 mm, shieldable, screw clamp, IP67 plugged and locked, UL 2237
Area	PBC15
Series	615
Part no.	99 6156 000 06

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).