

## Switching element - New Version

704.915.3-1



<https://www.eao.com/component/704.915.3-1/en/...>

Your product:



# 704.915.3-1

## Switching element - New Version

**ELECTRICAL CHARACTERISTICS**

**Switching voltage and switching current:**

|                                                                                                                 |                   |       |
|-----------------------------------------------------------------------------------------------------------------|-------------------|-------|
| as per DIN EN IEC 60947-5-1                                                                                     |                   |       |
| voltage                                                                                                         | DC13              | AC15  |
| 24 V                                                                                                            | 4.0 A             | 8.0 A |
| 60 V                                                                                                            | 1.5 A             | 8.0 A |
| 110 V                                                                                                           | 1.0 A             |       |
| 120 V                                                                                                           |                   | 8.0 A |
| 230 V                                                                                                           | 0.4 A             | 7.0 A |
| 400 V                                                                                                           | 0.2 A             | 5.0 A |
| 500 V                                                                                                           | 0.15 A            | 4.0 A |
| as per UL 60947-5-1                                                                                             |                   |       |
| voltage                                                                                                         | power             |       |
| 24 VDC                                                                                                          | 4.0 A, Pilot duty |       |
| 60 VDC                                                                                                          | 1.5 A, Pilot duty |       |
| 120 VDC                                                                                                         | 1.0 A, Pilot duty |       |
| 240 VDC                                                                                                         | 0.4 A, Pilot duty |       |
| 415 VDC                                                                                                         | 0.2 A, Pilot duty |       |
| 480 VDC                                                                                                         | 0.14A, Pilot duty |       |
| 120 VAC                                                                                                         | 8.0 A, Pilot duty |       |
| 240 VAC                                                                                                         | 7.0 A, Pilot duty |       |
| 415 VAC                                                                                                         | 5.0 A, Pilot duty |       |
| 480 VAC                                                                                                         | 4.0 A, Pilot duty |       |
| For voltages greater than $U_e = 400\text{ V}$ ,<br>the grid dimensions must not be<br>less than 35 mm x 50 mm. |                   |       |

**Contacts:** 2 NO

**Rated impulse withstand voltage Uimp:** 4 kV

**Rated insulation voltage Ui:** 500 V

|                                              |                      |        |         |
|----------------------------------------------|----------------------|--------|---------|
| <b>Recommended minimum operational data:</b> | Gold-silver contacts |        |         |
|                                              | Voltage              | 24 VDC | 110 VDC |
|                                              | Current              | 5 mA   | 2 mA    |
|                                              | Hard silver contacts |        |         |
|                                              | Voltage              | 24 VDC | 110 VDC |
|                                              | Current              | 50 mA  | 10 mA   |

**Switching rating:** 500 V AC @ 6 A

**Electrical lifetime:** 50 000 cycles of operation (500 VAC, 10 A)

**Pollution degree:** 3

**Standards:** The switches comply with the “Standards for low-voltage switching devices” DIN EN IEC UL 60947-5-1

**Thermal current I<sub>th</sub>:** Max. current as per EN IEC 60947-5-1 10 A

## MECHANICAL CHARACTERISTICS

**Terminal:** Plug-in terminal, 6.3 x 0.8 mm

**Contact material:** Silver

**Switching system:** Slow-make switching element

**Switching system:** The double-break, slow-make switching element is equipped with one or two independent contact systems, acting as normally open or normally closed contact. The normally closed contact has forced opening. Slow-make contacts with forced action are ideal for high switch ratings.

**Operating force:** 1 Normally closed approx. 2 N, 1 Normally open approx. 3 N

**Wire cross section:** Plug-in terminal 1 x 6.3 mm x 0.8 mm or 2 x 2.8 mm x 0.8 mm  
For switches with plug-in terminals it is necessary to provide insulation sleeves and to maintain a spacing of 65 mm between rows (mounting cut-outs).

**Weight:** 0.028 kg

## AMBIENT CONDITION

**IP Protection:** IP00

**Operating temperature:** – 40 °C ... + 55 °C

**Storage temperature:** – 40 °C ... + 85 °C

**Shock resistance:** (single impacts, semi-sinusoidal) 300 m/s<sup>2</sup>, pulse width 18 ms, as per DIN EN 60068-2-27

**Vibration resistance:** (sinusförmig) 100 m/s<sup>2</sup> bei 10 Hz...500 Hz, nach DIN EN 60068-2-6, Erhöhtes Breitbandrauschen nach DIN EN 61373, Klasse 1B

**Climate resistance:** Relative humidity 10 %rh ... 95 %rh (non-condensing) original packaging according to DIN EN IEC 60721-3-1 Class 1C1

## CERTIFICATE

**Approbations:** CB (IEC 60947-5-1), cULus, DNV, VDE

**Conformities:** CE, CCC, UKCA

**REACH:** REACH compliant

**RoHS:** RoHS compliant

## OTHER

**Short Description:** Switching element - New Version, Slow-make switching element, 500 V AC @ 6 A, Silver, 2 NO, Plug-in terminal, 6.3 x 0.8 mm

**Hints:** When using the switching element, the application guidelines must be observed.


For the third switching element the terminal marking insert is to be ordered separately  
 Operating temperature: Other temperatures on request  
 A suitable enclosure is required for applications with increased protection requirements. In North America, the product must be installed in an enclosure in accordance with UL 50E Type 2 or higher.

**Special requirements:**

Special requirements for positive-opening auxiliary current switches  
 Positive opening travel  
 Minimum force  
 Max. travel

Emerg  
 Emerg  
 which i  
 Emerg

**Wiring diagrams:**



**Dimension drawings:**

