

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 5 mm ... 10 mm, shielding: no, connecting thread: M16 x 1.5, color: silver-gray RAL 7001

Your advantages

- Plastic material conforms to UL 746C f1

Commercial data

Item number	1411124
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DCX
Product key	AF7DCX
Catalog page	Page 686 (C-2-2019)
GTIN	4046356922524
Weight per piece (including packing)	9.815 g
Weight per piece (excluding packing)	9.27 g
Customs tariff number	39269097
Country of origin	TR

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Technical data

Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---


Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BM-01
Shielded	no
Execution of the strain relief	A

Characteristics

Category of shock impact	2
Design, Strain relief	A

Dimensions

Dimensional drawing	
Length	39 mm
Length of the connecting thread	10 mm
Hole diameter	16.1 mm ... 16.2 mm
Wrench size, union nut	22 mm
Wrench size, support	22 mm
Hexagon angular dimension	25 mm
Thread type connection side	M16 x 1.5
Thread pitch	1.5 mm

Connection data

Tightening torque	2.5 Nm $\pm$ 0.5 Nm (Cap nut)
	2.5 Nm (Support sleeve)

Material specifications

Color	silver grey (RAL 7001)
Material Housing	PA (Housing)
Flammability rating according to UL 94	V2
Seal material Cable seal	CR

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Material for screw connection	PA
-------------------------------	----

Cable/line

External cable diameter Cable 1	5 mm ... 10 mm
External cable diameter	5 mm ... 10 mm (for UL 514 B)
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Enclosure rating (NEMA)	1
	4
	4X
	12
	13
Ambient temperature (operation)	-40 °C ... 100 °C (static)

G-INS-M16-S68N-PNES-GY - Cable gland


1411124

<https://www.phoenixcontact.com/gb/products/1411124>



Drawings

Dimensional drawing



Dimensional drawing

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1411124>

DNV

Approval ID: TAE00003WX



CSA

Approval ID: 115116



cUL Recognized

Approval ID: E199260



UL Recognized

Approval ID: E199260



VDE approval of drawings

Approval ID: 40024418

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Classifications

ECLASS

ECLASS-13.0	27140801
-------------	----------

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

G-INS-M16-S68N-PNES-GY - Cable gland



1411124

<https://www.phoenixcontact.com/gb/products/1411124>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk