



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
Primary Product Color: **White**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Retention Type	Latch
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Polyamide 6.6 GF
Centerline (Pitch)	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	3200
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1217092-2
PL 250 TERMINAL REC 16-12 AWG TPBR

TE Part # 63933-1
PL .250 TERMINAL REC 22-18 AWG BR

TE Part # 1217092-1
PL 250 TERMINAL RECEPTACLE 16-12 AWG BR

TE Part # 63854-1
250 PL MKIII REC. 18-14AWG BR

TE Part # 63933-2
250 PL MKIII REC. 22-18AWG TPBR

TE Part # 63854-2
250 PL MKIII REC. 18-14AWG TPBR

TE Part # 953043-1
PL LOCKING LEVER 3P HOUSING PA6. 6 NOIR

Also in the Series | Positive Lock 187

Crimp Terminal Housings(85)

Insertion & Extraction Tools(2)

Insulation Boots & Sleeves(7)

Quick Disconnects(57)

Customers Also Bought

TE Part #142685-3
L.I.F PL CONTACT 5MM 0.35-1 MM2 PTPPHBZ


TE Part #60742-2
187 FASTON REC 18-14 AWG TPBR

TE Part #142686-1
L.I.F PL CONTACT 5MM 1 TO 3 MM2 PTPPHBZ

TE Part #280000-6
250 FASTON,REC.,24-17 AWG,TPBR



TE Part #3-520124-2
187 ULTRA-FAST ASY REC 16-14 AWG
TPBR



TE Part #929971-1
BU-KONTAKT 2,5MMD

Documents

Product Drawings

PL 187 REC HSG 2P NYLON WHITE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_142680-9_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_142680-9_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_142680-9_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

French