




Connectors > Contacts > Connector Contacts > 2.54mm FFC Connectors Pin Contacts



Contact Type: **Pin**
 Contact Mating Area Plating Material: **Gold (Au)**
 Compatible With Wire & Cable Type: **Discrete Wire**
 Wire Size: **.12 – .4 mm²**

[All 2.54mm FFC Connectors Pin Contacts \(33\)](#)

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

	30 μin
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
Product Terminates To	Wire & Cable

Dimensions

Accepts Conductor Width	1.27 mm, 2.33 mm
-------------------------	------------------



Compatible Insulation Diameter Range	1.02 – 1.42 mm [.04 – .056 in]
--------------------------------------	--------------------------------

Wire Size	.12 – .4 mm ²
-----------	--------------------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C [-85 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---




Solder Process Capability	Reflow solder capable to 260°C
---------------------------	--------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 <p>TE Part # 1-485893-1 013 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 3-88190-0 010 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 3-88189-0 010 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 485893-4 006 HOUSING FFC PIN 100CL SR</p>
 <p>TE Part # 485893-2 004 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 485893-8 010 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 58535-1 PRO-CRIMPER ASSY MODU MODII</p>	 <p>TE Part # 58535-2 PRO-CRIMPER ASSY MODU</p>
 <p>TE Part # 1-485893-6 018 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 3-88190-2 006 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 1-88190-8 040 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 1-485893-3 015 HOUSING FFC PIN 100CL SR</p>
 <p>TE Part # 1-88190-2 026 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 3-88189-2 006 HOUSING FFC PIN DR 100CL</p>	 <p>TE Part # 485893-7 009 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 485897-2 004 HOUSING FFC PIN 100CL SR</p>
 <p>TE Part # CAT-F439-R2435254 2.54mm FFC Connectors Receptacle Housing</p>	 <p>TE Part # 485893-5 007 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 485893-9 011 HOUSING FFC PIN 100CL SR</p>	 <p>TE Part # 485893-3 005 HOUSING FFC PIN 100CL SR</p>

Customers Also Bought




TE Part #CAT-F439-R2435254
2.54mm FFC Connectors Receptacle Housing



TE Part #207464-2
CRIMP SNAP PLUG ASSY, SZ 3



TE Part #485893-2
004 HOUSING FFC PIN 100CL SR




TE Part #3-1437020-7
609-1031HD=FSKT IDC S 10 SR



TE Part #1-1437719-4
T01-0540-S05-FEMALE PLUG CONNECTOR-CRIMP




TE Part #5-1437720-6
T01-CRIMP-S03



TE Part #1546348-2
R/A CABLE CLAMP KIT, SZ 13, CPC



TE Part #1-1564559-1
4POS, MCON 1.2 LL TAB SEALED COD A



TE Part #3-1437602-2
SMCPK=SW BI-DIRECTIONAL

Documents

Product Drawings

[ROUND WIRE PIN L.P.](#)

English

[ROUND WIRE PIN L.P.](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_86561-4_D.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_86561-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_86561-4_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Application Specification

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Extraction Tool for Flexible Flat Cable (FFC)

English