




AMP-IN

TE Internal #: 172520-4
Board-In PCB Mount One-Piece Crimp Connector, Vertical, Wire-to-Board, 4 Position, 2.5 mm [.098 in] Centerline, Discrete Wire, Natural, 4 A, Signal

[View on TE.com >](#)

Connectors > PCB Connectors > Board-In Connectors



PCB Connector Type: **PCB Mount One-Piece Crimp Connector**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **4**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

PCB Connector Type	PCB Mount One-Piece Crimp Connector
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board, Wire & Cable

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	4
Compatible With Wire & Cable Type	Discrete Wire
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

--	--



Contact Current Rating (Max)	4 A
------------------------------	-----

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
Housing Material	66 Nylon

Dimensions

Wire Size	30 – 26 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products






will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

			
TE Part # 172782-7 LOW PROFILE MINI AMP-IN	TE Part # 172781-4 LOW PROFILE MINI AMP-IN (AWG#30-#26)Y-TY	TE Part # 172781-3 LOW PROFILE MINI AMP-IN (AWG#30-#26)X-TY	TE Part # 172782-5 LOW PROFILE MINI AMP-IN

Customers Also Bought

			
TE Part #1571100-2 PRCSD1-20F-BB0DW,POWER ROCKER	TE Part #280530-2 AMP MODU MOD 2 CONT	TE Part #338095-6 MICRO-MATCH COSIHSG	TE Part #160831-4 PL REC 1.0-2.5 MM2 .0160 X 2.060 TPPHBZ
			
TE Part #338069-4 MICRO-MATCH SMD FTE	TE Part #167296-1 50P.HDP20 PLUG ASSY	TE Part #104479-2 SHORT POINT CONT PLTD SN-PB	TE Part #2317570-1 AV22 SPM 3A MOVING RING R&G 12V
			
TE Part #208210-2 METRIMATE SOCKET 19 POSN	TE Part #643314-1 08P UMNL STR/REL		

Documents

Product Drawings



LOW PRO MINI AMP-IN HDR 4P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_172520-4_G1.3d_stp.zip

English

Customer View Model

ENG_CVM_172520-4_G1.2d_dxf.zip

English

Customer View Model

ENG_CVM_172520-4_G1.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_172520-4_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_172520-4_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_172520-4_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English

Application Specification

English

Agency Approvals

UL Report

English

UL Report

English